



SUPPLY	CONSUMPTION	AUX. CONTACTS		CODE (1)
		NO	NC	
AC	4.5 VA	4	-	40
		3	1	31
		2	2	22

CA-KN RELAYS			
VOLTS AC 50/50 HZ	CODE (2)	CODE (3)	CODE (4)
12	J7	JD	JW3
24	B7	BD	BW3
36	C7	CD	
42	D7		
48	E7	ED	EW3
60		ND	
72		SD	SW3
100		KD	
110	F7	FD	
120	B7		
125		GD	
127	FC7		
208	L7		
220		MD	
220/230	M7		
230	P7	MPD	
230/240	U7		
240		MUD	
250		UD	
380/400	Q7		
400	V7		
400/415	N7		
440	R7		
480	T7		
500	S7		
600/660	Y7		

CA2KN = AC CONTROL RELAY
 CA3KN = DC CONTROL RELAY
 CA4KN = DC LOW CONSUMPTION CONTROL RELAY

Catalog Number: CA2KN(1)(2), CA3KN(1)(3), CA4KN(1)(4)
 Ratings: -
 UL File/Class: -
 CSA File/Class: -
 Meets Standards: IEC 947, NF C 63-140, VDE 0660, BS 5424, CE
 Weight: -
 Wire Size: MINI (1) 16 AWG, MAX (2) 12 AWG
 Terminal Torque: 7 LB-IN
 Mounting Hwd.: 35mm DIN TRACK OR PANEL MOUNT

DUAL DIMENSIONS: INCHES
 MILLIMETERS

IEC INDUSTRIAL CONTROL RELAY (K-LINE)
 CA2KN(1)(2), CA3KN(1)(3), CA4KN(1)(4)



DWG# E0702001-01
 NO.