

## Easy UPS 3L

### Classic Battery Runtimes

Battery runtimes are listed in minutes.

Battery runtimes are estimated values based on battery manufacturer data for operation at 25 °C.

Please note that not all battery solutions are available for all UPS ratings due to:

- The specific battery solution would provide less than 5 minutes runtime with the specific UPS.

UPS rating	250 kVA				300 kVA				400 kVA			
Power factor	1											
	25% load	50% load	75% load	100% load	25% load	50% load	75% load	100% load	25% load	50% load	75% load	100% load
E3MCBC10B	21	6.8										
E3MCBC10C	24	8.3										
E3MCBC10D	36.5	15	8.3	5	29	11.5	6.1		20	7.5		
E3MCBC10E	52	21	11	6.7	41.5	16	8.3		28.5	10		
2 x E3MCBC7D	26	10	5.4		20.5	8						
2 x E3MCBC10A	36.5	15	8.3	5	28.5	11	5.9		20	7.5		
2 x E3MCBC10B	52	21	11	6.7	41.5	16	8.3		28.5	10		
2 x E3MCBC10C	59.5	24.5	13.5	8.2	47.5	19	10	5.6	32.5	12	5.7	
2 x E3MCBC10D	83.5	37	22	15	67.5	29.5	17.5	11.5	48	20.5	11.5	7.4
2 x E3MCBC10E	120	52.5	31	21	97	42	24.5	16	68.5	28.5	16	10
3 x E3MCBC7C	26.5	10.5	5.5		21	8						
3 x E3MCBC7D	43	18	10	6.5	34.5	14	8		24	9.5		
3 x E3MCBC10A	59.5	26	15	9.9	47	20	11	7.2	33.5	13.5	7.5	
3 x E3MCBC10B	85.5	36.5	21	13.5	68.5	28.5	16	10	48	19	10	5.8
3 x E3MCBC10C	97	42	24.5	16	78	33	19	12	55	22.5	12	7.2
3 x E3MCBC10D	130	60	37	25.5	105	48.5	29.5	20	77.5	34	20.5	13.5
3 x E3MCBC10E	190	86.5	52.5	36	155	69.5	41.5	28.5	110	48.5	28.5	19

UPS rating	500 kVA				600 kVA			
Power factor	1							
	25% load	50% load	75% load	100% load	25% load	50% load	75% load	100% load
E3MCBC10E	21	6.8						
2 x E3MCBC10B	21	6.8						
2 x E3MCBC10C	24.5	8.3						
2 x E3MCBC10D	37	15	8.3		29.5	11.5	6.1	
2 x E3MCBC10E	52.5	21	11	6.7	41.5	16	8.3	

UPS rating	500 kVA				600 kVA			
Power factor	1							
	25% load	50% load	75% load	100% load	25% load	50% load	75% load	100% load
3 x E3MCBC7C								
3 x E3MCBC7D	18	6.8						
3 x E3MCBC10A	25.5	10	5		20	7.5		
3 x E3MCBC10B	36.5	13.5	6.7		28.5	10		
3 x E3MCBC10C	41.5	16	8.3		33	12	5.7	
3 x E3MCBC10D	60	26	15	9.9	48	20.5	11.5	7.4
3 x E3MCBC10E	86	36.5	21	13.5	69	28.5	16	10