

TANÚSÍTVÁNY

Certificate



Tanúsítvány szám *Certificate No.*
HN 69290353

Oldal *Page*
0001

Jegyzőkönyvszám *Test Report No.*
CN21R87B 001

Kiadás dátuma *Date of Issue*
2021-07-20

Tanúsítvány Tulajdonos *Certificate Holder*
Schneider Electric Industries
SAS
35 Rue Joseph Monier
92506 Reuil Malmaison, Cedex
France

Gyártóhely *Manufacturing Plant*
NINGBO YUSING LIGHTING CO., LTD.
NO.1199, Mingguang RD. Jiangshan
Town, Ningbo, 315195 Zhejiang, P.R.
China

Vizsgálati Jel *Test Mark*



Tanúsítás alapjául szolgáló előírások *Tested according to*

EN 60598-2-1:1989
EN 60598-2-5:2015
EN 60598-1:2015+A1

Tanúsított Termék (Termék azonosítás)
Certified Product (Product Identification)

Floodlight (LED Floodlight)

Type Designation: IMT47222, IMT47223, IMT47224

Ratings:

Rated voltage: AC 220-240V; 50/60Hz

Protection Class: I

Degree of Protection: IP65

ta: 25°C

Trade Mark: Schneider Electric

See details in the Annex of this certificate.

A tanúsítvány a fenti termék típusra vonatkozik. A tanúsítvány a TÜV Rheinland InterCert Kft. Vizsgálati, Ellenőrzési és Tanúsítási Szabályzatán alapszik. A tanúsított termék megfelel a fenti vizsgálati előírásoknak, a sorozatgyártása ellenőrzött. A fenti ENEC jel használatának joga engedélyezett a tanúsított terméken. Ezt az Engedélyt egy ENEC egyezményt aláíró testület adta ki. This certificate refers to the above mentioned product type. The certificate is based on the Testing, Inspection and Certification Regulation of TÜV Rheinland InterCert Kft. The certified product fulfils the above listed requirements and its manufacturing is subject to surveillance. The right to use the above ENEC mark is permitted on the certified product. This Licence has been established by a body which is a signatory to the ENEC Agreement.

TÜV Rheinland InterCert Kft., MEEI Division – Product Certification
H-1143 Budapest, Gizella út 51-57., Hungary
www.tuv.com

Tanúsító Szervezet
Certification Body

Guoping Zheng

Validity of certificate can be checked on www.CERTIPEDIA.com

Annex to certificate No. HN 69290353 0001

Page 1/1

Model List:

Model No.	Rated voltage	Rated wattage	Driver	LED type	CCT
IMT47222	AC 220-240V, 50/60Hz	150W	ELG-150-48A	SMD 2835 1W 9V	3000K, 4000K, 5000K, 6500K
IMT47223		200W	ELG-200-48A		
IMT47224		300W	2xELG-150-48A		


TÜVRheinland[®]**Date of issue:**
Budapest, 2021-07-20**Certification Body**.....
Guoping Zheng