


# CERTIFICATE FI 30014



Our Ref. 289487

**Product** Socket-outlet

**Type** 270/\*\*\*

**Trade mark**  Schneider Electric

**Certificate Holder** Schneider Electric Industries SAS  
35, rue Joseph Monier, 92500 RUEIL MALMAISON,  
FRANCE

**Manufacturer** Schneider Electric Industries SAS  
35, rue Joseph Monier, 92500 RUEIL MALMAISON,  
FRANCE

**Technical information** 16 A, 250 V~, IP20 / 21 / 44

**Other information** Standard sheet CEE 7 / III  
One fold flush-type fixed socket-outlet. With screw terminals. With and without shutters.  
Screw- or claw fixing.  
Socket-outlet list, see appendix 1 and 2

**The product is certified according to the following standard(s)** IEC 60884-1:2002 (Ed 3) + A1:2006 + A2:2013  
SFS 5610:2015 + A11:2016

**Validity** This certificate is valid until 06 July 2022 provided that the Conditions for FI certification are met. This certificate includes the right to use the FI mark under the condition that product changes (if any) will be approved at SGS Fimko before the product is brought onto market.

**Date of issue** 06 July 2017

**SGS Fimko Ltd**

**Signature**



Matti Huttunen  
Certification Engineer

This certificate has 2 appendixes



This certificate is issued by the company under its General Conditions for Certification Services accessible at <http://www.sgs.fi/en/Terms-and-Conditions.aspx>. Attention is drawn to the limitations of liability defined therein and in the Test Report here above mentioned which findings are reflected in this certificate. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

**Manufacturing sites**

Merten GmbH  
Fritz-Kotz-Strasse 8, D-51674 WIEHL-BOMIG,  
GERMANY

**Additional information**

The product has certificate 1620519 issued by Intertek Semko AB in accordance with the Nordic Certification Service system.



Socket-outlet type list:

**System Basis (Thermo/Duro)**  
270/2744, 270/2746, 270/2742, 270/2743, 270/2704, 270/2304

**System M (Thermo/Duro)**  
270/2371, 270/2373, 270/2376, 270/2374, 270/2300, 270/2301, 270/2309 with or without LED light module 2003, 270/2474, 270/2485, 270/2496, 270/2470, 270/2471, 270/2472, 270/2473, 270/2334 with LED light module 2334

**System Design (Thermo/Duro)**  
270/2375, 270/2377, 270/2372, 270/2379 with or without LED light module 2003, 270/2378, 270/2306, 270/2308, 270/2478, 270/2476, 270/2477

**OctoColor**  
270/2740, 270/2702, 270/2740

**AQUADESIGN**  
270/2330, 270/2335

**Renova**  
270/EAV54699

**Robust**  
270/101363, 270/EAV54699, IK class IK09  
**Trend**  
270/NVE66783

Frame types:

**System Basis (Thermo+Duro)**  
**Atelier, M1: (1 - 3 gang)**  
3871, 3872, 3873, 3874, 3875

**System M (Thermo+Duro)**  
**M-Smart: (1 - 5 gang)**  
4841, 4842, 4843, 4844, 4845

**1M: (1 - 5 gang)**  
3891, 3892, 3893, 3894, 3895

**M-Plan II: (1 - 3 gang)**  
4881, 5124, 4882, 5125, 4883, 5126

**M-Plan: (1 - 5 gang)**  
4861, 4862, 4863, 4864, 4865

**M-Plan Metall: (1 - 5 gang)**  
4751, 4752, 4753, 4754, 4755

**M-Plan Echtglas: (1 - 5 gang)**  
4801, 4802, 4803, 4804, 4805

**M-ARC: (1 - 5 gang)**  
4851, 4852, 4853, 4854, 4855

**M-Star: (1 - 5 gang)**  
4871, 4872, 4873, 4874, 4875

**Atelier-M: (1 - 5 gang)**  
3881, 3882, 3883, 3884, 3885

## Appendix 2 to Certificate 30014

**System M – Elegance: (1 - 5 gang)**  
 4021, 4022, 4023, 4024, 4025, 4031, 4032, 4033, 4034, 4035  
 4041, 4042, 4043, 4044, 4045, 4051, 4052, 4053, 4054, 4055

**System M – Extract (Thermo)**  
**Basic: (1 - 5 gang)**  
 BBV49550, BBV49551, BBV49552, BBV49553, BBV49554

**Design: (1 - 3 gang)**  
 BBV49558, BBV49559, BBV49561

**Solid: (1 - 4 gang)**  
 BBV49558, BBV49559, BBV49561, BBV49589

**Solid Glass: (1 - 4 gang)**  
 S1A45091, S1A45092, S1A45094, S1A45092

**Combi: (1 - 5 gang)**  
 BBV49575, BBV49576, BBV49577, BBV49578, BBV49580

**Primo: (1 - 6 gang)**  
 BBV49583, BBV49584, BBV49587, BBV49585, BBV49586, BBV54904, BBV54905

**Gasket for all IP44 frames: (1 - 3 gang)**  
 BBV49557, S1A33102, S1A33103

**System M – Creathr (1 - 5 gang)**  
 4010-35, 4020-35, 4030-35, 4040-35, 4050-35, 4025-35, 4035-35,

**System Design (Thermo + Duro)**  
**ARTEC, Antik, Filiche: (1 - 5 gang)**  
 4811, 4812, 4813, 4814, 4815, 4831, 3981, 3982, 3983, 3984, 3985

**TRACENT: (1 - 4 gang)**  
 4821, 4822, 4823, 4824

**OctoColor: (1 - 5 gang)**  
 3981, 3982, 3983, 3984, 3985, 3986

**AQUADESIGN: (1 - 4 gang)**  
 4011, 4012, 4013, 4014

**Renova**  
**Glass frame: (1 - 3 gang)**  
 BBV28342, BBV28343, BBV28344  
**Plastic frame: (1 - 5 gang)**  
 101370, 101371, 101372

**Robust:**  
 Center Cover Adapter 101599

**Trend:**  
 100520 (1-gang)  
 100521 (2-gang)  
 100522 (3-gang)  
 100523 (4-gang)  
 101524 (5-gang)

This certificate replaces previous certificate FI 29300 A1 dated 23 November 2015. The standard has been updated and the different constructions have been added.

Our ref. no.

289487-1