

# CERTIFICATE FI/40868/A1

Our Ref. HEL-CERT201100533-02



**Product** Light dimmer

**Type** 315GLE, 630GLE, SBD315RC, SBD630RC,  
SBD400R-1, SBD400R-2, SBD400RL, SBD600RL

**Trademark**  or 

**Certificate Holder** Schneider Electric Industries SAS  
35 Rue Joseph Monier, 92500, Rueil-Malmaison, France

**Technical information** **315GLE, SBD315RC:** 230V~, 50Hz, 20-315W  
**630GLE, SBD630RC:** 230V~, 50Hz, 20-630W  
**SBD400R-1, SBD400R-2, SBD400RL:** 230V~, 50Hz, 40-400W  
**SBD600RL:** 230V~, 50Hz, 40-600W

IP20, IP44 (for special Exxact cover, frame and gasket)

**Other information** Electronic dimmer for flush mounting. Screw type terminals.  
µ-gap disconnection. Pattern no. 1 or 6.

**The product is certified according to the following standard(s)** EN 60669-1:1999 + A1:2002 + A2:2008  
EN 60669-2-1:2004 + A1:2009 + A12:2010

**Validity** This certificate is valid until 24 November 2025 provided that the Conditions for FI certification are met. This certificate includes the right to use the FI mark under the condition that changes (if any) will be checked at SGS Fimko before the product is brought onto market and that the conditions for FI certification are met.

**Date of issue** 31 October 2023

**SGS Fimko Ltd**

**Signature**



Mikko Välimäki  
Certification Manager






























**Manufacturer** Schneider Electric Industries SAS  
35 Rue Joseph Monier, 92500, Rueil-Malmaison, France

**Manufacturing site** GPV Estonia AS  
Valga mnt. 7 A, EE-61504, Elva, Estonia

**Directive information** The certified product(s) fulfils requirements of mentioned standard(s) which are harmonised under the Low Voltage Directive (2014/35/EU) at the date of issue of the certificate.

**Additional information** The products have certificate No. SE-S-2002606 issued by Intertek Semko AB in accordance with the Nordic Certification Service system.

Model	Incandescent (W)	Electronic step-down converter (VA)	Iron-core transformer (VA)	Pattern	Brand
315GLE	20 - 315	20 - 315	-	6	
630GLE	20 - 630	20 - 630	-	6	
SBD315RC	20 - 315	20 - 315	-	6	
SBD630RC	20 - 630	20 - 630	-	6	
SBD400R-1	40 - 400	-	-	1	
SBD400R-2	40 - 400	-	-	6	
SBD400RL	40 - 400	-	40 - 400	6	
SBD600RL	40 - 600	-	40 - 600	6	

Cover design	Center button/cover	Frames (all 1-5 gang)	Brand
RS 16	L3034	L571	
Elko Plus	L3303	L3295+L3291	
Trend	100949	100520	
Trend Solid	100949	101543 (plastic, glass, metallic)	
Renova/Arezzo	101368	101370	
Artic	13620	13601	
Artic Décor	13620	13806 (plastic, glass, metallic)	
Senso	20005157	20005048+20005050	
Fashion	227010-0-1	224100-0-1	
Riva	227010-0-1	204120-0-1	
Scala	227010-0-1	21169.70-0:1	
Novia	100634	100600, ring: 21179.50-0:2	
Classic	227010-0-1	21169.151-0:1	
Joy	267010-0-1	264100-0-1	
M-Plan II	5699	4881	
M-Plan	5699	4861	
M-Plan metal	5699	4751	
M-Plan real glass	5699	4891	
M-Arc	5699	4851	

**Page 2 of 3**

This document is issued by the Company under its General Conditions of Service accessible at [http://www.sgs.com/terms\\_and\\_conditions.htm](http://www.sgs.com/terms_and_conditions.htm). Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein.

Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

**SGS Fimko Ltd**

Takomotie 8, FI-00380 Helsinki, Finland  
t. +358 9 696 361 [www.sgs.fi](http://www.sgs.fi)

Business ID 0978538-5

Member of the SGS Group (SGS SA)

**Additional information**

Cover design	Center button/cover	Frames (all 1-5 gang)	Brand
M-Star	5699	4871	Schneider Electric
Atelier-M	5699	3881	Schneider Electric
1-M	5699	3891	Schneider Electric
M-Smart	5699	4841	Schneider Electric
M-Creative	BBV35736	4010-35	Schneider Electric
Elegance	5699	4021, 4031, 4041, 4051	Schneider Electric
M-Pure/M-Pure	5699	4010-36	Schneider Electric
Artec	5720	4811 (plastic, glass, metallic)	Schneider Electric
Antik	5720	4831 (plastic, metallic)	Schneider Electric
Tracent	5720	4821	Schneider Electric
D-Life	NHA5193102	NHA2920502, NHA2923102, NHA2922102	Schneider Electric
Forum	13620	W450104	Schneider Electric
Duet	Not specified	Not specified	Schneider Electric
Wessen 59	Not specified	Not specified	Schneider Electric
Odace	BBV4007302	S520702X, S520802X, S5X0802X	Schneider Electric
Asfora	300802-xx, 300801-xx	300101-xx	Schneider Electric
Sedna	100821/100822	100101	Schneider Electric
Unica	2004912	6.002.---	-
Exxact	BBV39712	Combi (BBV49575), Basic (BBV49550), Primo (BBV49558 or BBV49583), Solid (BBV49558), Solid Glass (S1A45091)	Schneider Electric

This certificate replaces previous certificate FI/40868, dated 2020-11-24, due to the factory's name change.

As shown in the Test Report(s) No(s): 226539-TL3-1, 226540-TL3-2