


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
HDA261252


 by **Schneider Electric**
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:
 General Application: Provides overload and short circuit protection
 For Use With: I-line Panelboards and Switchboards
 Approvals: UL Listed - CSA Certified - IEC Rated
 Mounting Type: I-Line Plug-On
 Terminal Type: I-Line Connection (ON end) - Lugs (OFF end)
 Wire Size: #14-3/0 AWG (Al/Cu)
 Weight: 5 Pounds
 Mounting Height: 3 Inches

Specification:
 Description: PowerPact H-frame Thermal Magnetic Circuit Breaker
 Number of Poles: 2-Pole
 Ampere Rating: 125A
 Voltage Rating: 600VAC
 Interrupting Rating: 25kA at 240VAC - 18kA at 480VAC - 14kA at 600VAC
 Fixed AC Magnetic Trip: Hold: 900A - Trip: 1700A
 Phase Connection: AC