



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**HGA36015**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

**General Application:** Provides overload and short circuit protection  
**For Use With:** I-line Panelboards and Switchboards  
**Approvals:** UL Listed - CSA Certified - IEC Rated  
**Mounting Type:** I-Line Plug-On  
**Terminal Type:** I-Line Connection (ON end) - Lugs (OFF end)  
**Wire Size:** #14-3/0 AWG (Al/Cu)  
**Weight:** 5 Pounds  
**Mounting Height:** 4.5 Inches

**Specification:**

**Description:** PowerPact H-frame Thermal Magnetic Circuit Breaker  
**Number of Poles:** 3-Pole  
**Ampere Rating:** 15A  
**Voltage Rating:** 600VAC  
**Interrupting Rating:** 65kA at 240VAC - 35kA at 480VAC - 18kA at 600VAC  
**Fixed AC Magnetic Trip:** Hold: 350A - Trip: 750A  
**Phase Connection:** ABC