



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
HGL36050C



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

General Application: Provides overload and short circuit protection
 For Use With: Industrial Enclosures and Switchboards
 Approvals: UL Listed - CSA Certified - IEC Rated
 Mounting Type: Unit Mount
 Terminal Type: Line: Lug - Load: Lug
 Wire Size: #14-3/0 AWG(Al/Cu)
 Weight: 5 Pounds
 Depth: 4.36 Inches
 Height: 6.40 Inches
 Width: 4.12 Inches

Description: PowerPact H-frame Thermal Magnetic Circuit Breaker
 Number of Poles: 3-Pole
 Ampere Rating: 50A
 Voltage Rating: 600VAC/250VDC
 Interrupting Rating: 65kA at 240VAC - 35kA at 480VAC - 18kA at 600VAC - 20kA at 250VDC
 Circuit Breaker Rating: 100% Rated
 Fixed AC Magnetic Trip: Hold: 400A - Trip: 850A

Specification: