



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:  
**HMIPUF6D0701**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

Rated Voltage: 24 VDC  
 Memory: 2GB RAM  
 Hard Drive: 60GB SSD  
 Power Consumption: 130 W Max.  
 Cooling: Fanless  
 Degree of Protection: IP 65, NEMA 4x (indoor use)  
 Operating Temperature.: 0°C to 50°C (32 to 122°F)  
 Storage Temperature: -20 to 60°C (-4 to 140°F)  
 CPU: Celeron 827E - 1.40 GHz  
 Supported OS: Windows® 7 Ultimate (32-bit)

Description:  
 Graphics: XGA TFT (1024 x 768 pixels)  
 Colors: 16 million  
 Brightnes: 375 cd/m2  
 Touch Screen: Analog Resistive Film  
 Serial Interface: 2x RS232C  
 USB: 4x USB 3.0, 1x USB 2.0 (front panel)  
 Ethernet: 2x 10/100/1000 Mbps  
 Video Output: DVI  
 Expension Slot: 0

**Specification:**

Magelis 12" Panel PC - Universal  
 XGA TFT (1024 x 768 pixels)  
 16 million  
 375 cd/m2  
 Analog Resistive Film  
 2x RS232C  
 4x USB 3.0, 1x USB 2.0 (front panel)  
 2x 10/100/1000 Mbps  
 DVI  
 0