

8 7 6 5 4 3 2 1

D
C
B
A






D
C
B
A

MOUNTING
HARDWARE M10

AIR EXHAUST

CUSTOMER CONNECTIONS

AIR INLET



- NOTES:
1. IP00 TYPE ECLOSURE
 2. AMBIENT TEMP 0-40 C
 3. ALTITUDE 1000M(3300 FT)
 4. HUMIDITY -95% NON-CONDENSING
 5. INDOOR INSTALLATION IN CLEAN ENVIRONMENT
 6. MINIMUM CLEARANCES:
182 MM ABOVE FOR AIRFLOW
220 MM BELOW FOR AIRFLOW AND IMPELLER SERVICE
 7. COMMERCIAL REFERENCE WILL INCLUDE HMI AND EXTENSION CABLES

	Scale: N/A	Tolerancing Standard: ISO8015	Units of Measure: mm
		FINISHED 60A IP00 <i>FINISHED 60A IP00</i>	
Number: HRB17292		Revision: 00	Sheet: 1 OF 1
All information and data contained in this document are the exclusive property of Schneider Electric Industries SAS and may neither be used nor disclosed without its prior written consent.			State:

8 7 6 5 4 3 2 1