





8 7 6 5 4 3 2 1

D
C
B
A



D
C
B
A



AIR EXHAUST



CUSTOMER CONNECTIONS
AIR INLET



NOTES:

1. IP00 TYPE ENCLOSURE.
2. AMBIENT TEMP. 0-40C.
3. ALTITUDE 1000M(3300FT).
4. HUMIDITY -95% NON-CONDENSING.
5. INDOOR INSTALLATION IN CLEAN ENVIRONMENT.
6. MINIMUM CLEARANCE
200mm ABOVE FOR AIRFLOW
400mm BELOW FOR AIRFLOW
7. MOUNTING HARDWARE: M10
8. DRAWING SCALE IS 1:15 EACH VIEW
9. HMI PROVIDED LOOSE WITH PRODUCT.
10. DXF FILE SCALE IS 1:15 EACH VIEW.

	Scale: N/A	Tolerancing Standard: ISO 8015	Units of Measure: MILLIMETERS
Schneider Electric			
TITLE: 300A FINISHED CHASSIS (IP00 ACCUSINE+)			
<i>TITLE: 300A FINISHED CHASSIS (IP00 ACCUSINE+)</i>			
Number: HRB18272		Revision: 00	Sheet: 1 OF 1

All information and data contained in this document are the exclusive property of Schneider Electric Industries SAS and may neither be used nor disclosed without its prior written consent.

State:

Released for Manufacturing
Printed on 2015/07/09

8 7 6 5 4 3 2 1