

Clipsal Iconic™ Electronic Mechanisms – Selection Chart



| Product Name | Smart PB Remote mech with LED | ControlLink Remote Mech | Rotary LED Dimmer 2-Wire | Rotary Uni Dimmer 2-Wire | PB Dimmer w CTL 2-Wire | PB Switch w CTL 2-Wire | PB Timer w CTL 2-Wire | Single Port 1.5A USB Charger | Dual Port 3.1A USB Charger | PIR Motion Sensor 3-Wire |
|--|--|---------------------------|---------------------------------------|---|---|---|---|------------------------------|----------------------------|--|
| Model # | 41EPBCLM-VW | 41EPBM-VW | 42E350RLD2M-VW | 42E350RUD2M-VW | 41E300PBUD2SM-VW | 41E350PBES2SM-VW | 41E350PBT2SM-VW | 40E1USBM-VW | 40E2USBM-VW | 41EPIRM-TN |
| 2-Wire/ 3-Wire | 3-Wire (Active, Neutral, ControlLink) | 2-Wire | 2-Wire | 2-Wire | 2-Wire | 2-Wire | 2-Wire | Active, neutral | Active, neutral | 3-Wire |
| Multiway control | Slave / Remote Control | Slave / Remote Control | Suitable for 1/2 way switching | Suitable for 1/2 way switching | Multiway dimming | Multiway switching | Multiway remote trigger | NA | NA | Can parallel multiple devices |
| Configurable LED indicator | YES | NO | NO | NO | YES | YES | YES | NA | NA | LED present but not configurable |
| Configurable min brightness | NA | NA | YES | YES | YES | NA | NA | NA | NA | NA |
| Min load | NA | NA | 1W | 1W | 10W | 10W | 10W | NA | NA | NA |
| Max load | ControlLink communication only, no direct load control | 240V 50mA | 350W | 350W | 300W | 350W | 350W | 1.5A | 2.1A per port (3.1A max) | 750W, 150W LED, M3(0.5A @0.5pf) |
| Timer range | NA | NA | NA | NA | NA | Infinite | 30s- 4hr | NA | NA | 10s - 15min |
| Built-in over-temp, overload, short circuit protection | NA | Overload | YES | YES | YES | YES | YES | YES | YES | Overtemp |
| Suitable for fan motors | NA | NO | NO | YES | NO | NO | NO | NA | NA | YES |
| Depth from grid Compatible wall box | 39mm standard | 39mm standard | 36mm standard | 36mm standard | 39mm standard | 39mm standard | 39mm standard | 37mm standard | 55mm deep | 41mm standard |
| No. of units in a plate | 6 | 6 | 3 (de-rating applies) | 3 (de-rating applies) | 6 (de-rating applies) | 6 (de-rating applies) | 6 (de-rating applies) | 3 | 2 | 3 |
| Application | Provides multiway control with matching LED indicator | Provides multiway control | Lighting – LED, halogen, incandescent | Lighting – LED, halogen, small fans, incandescent | Lighting – Clipsal LED, halogen, incandescent | Lighting – Clipsal LED, halogen, incandescent | Lighting – Clipsal LED, halogen, pantry, toilet | Kitchen, bedroom, study | Kitchen, bedroom, study | Hallway, stairs, pantry, W.I.R, entry, bathrooms |

clipsal.com/iconic

Clipsal Iconic™ BLE Mechanism – Selection Chart



| Product Name | Smart PB Remote mech with LED | PB Switch 6A w BLE 3-Wire | PB Timer 6A w BLE 3-Wire | PB Timer 10A w BLE 3-Wire | PB Time Clock 6A w BLE 3-Wire | PB Time Clock 10A w BLE 3-Wire | PB Wiser Dimmer 300W w BLE 3-Wire |
|--|--|---|---|--|---|---|--|
| Model # | 41EPBCLM-VW | 41E6PBES3SBM-VW | 41E6PBT3SBM-VW | 41E10PBT3SBM-VW | 41E6PBTC3SBM-VW | 41E10PBTC3SBM-VW | 41EPBDWCLM-VW |
| 2-Wire/ 3-Wire | 3-Wire (Active, Neutral, ControlLink) | 3-Wire | 3-Wire | 3-Wire | 3-Wire | 3-Wire | 3-Wire |
| Multiway control | Slave / Remote Control | Multiway switching | Multiway remote trigger | Multiway remote trigger | Multiway remote trigger | Multiway remote trigger | Multiway dimming |
| Smart device app configuration | NO | YES | YES | YES | YES | YES | YES |
| Configurable LED indicator | YES | YES | YES | YES | YES | YES | YES |
| Configurable min brightness | NA | NA | NA | NA | NA | NA | YES |
| Min load | NA | NA | NA | NA | NA | NA | NA |
| Max load | ControlLink communication only, no direct load control | 6AX/1440W 6A @ 0.8pf M30 (5A @ 0.5pf) | 6AX/1440W 6A @ 0.8pf M30 (5A @ 0.5pf) | 10AX/15A Res 10A @ 0.8pf M40 (6A @ 0.5pf) | 6AX/1440W 6A @ 0.8pf M30 (5A @ 0.5pf) | 10AX/15A Res 10A @ 0.8pf M40 (6A @ 0.5pf) | 300W |
| Timer range | NA | Infinite | 1s-24hr | 1s-24hr | 1s-24hr | 1s-24hr | 1s-24hr |
| 24hr / 7day schedule function | NA | NO | NO | NO | YES | YES | YES (with selectable dimming levels) |
| Built-in over-temp, overload, short circuit protection | NA | Overtemp | Overtemp | Overtemp | Overtemp | Overtemp | YES |
| Suitable for fan motors | NA | YES | YES | YES | YES | YES | NO |
| Depth from grid Compatible wall box | 39mm Standard | 39mm standard | 39mm standard | 70mm deep | 39mm standard | 70mm deep | 70mm deep |
| No. of units in a plate | 6 | 6 (de-rating applies) | 6 (de-rating applies) | 3 (de-rating applies) | 6 (de-rating applies) | 3 (de-rating applies) | 3 (de-rating applies) |
| Application | Provides multiway control with matching LED indicator. | All lighting, exhaust fans, contactors, sensors | All lighting, exhaust fans, garden lights, pumps, decorative lights | All lighting, exhaust fans, outdoor heater, pumps, garden lights | All lighting, exhaust fans, pumps, garden lights, heated towel rail | All lighting, exhaust fans, pool pump, HWS booster, garden lights | LED, halogen, incandescent, bedrooms, lounge, dining, family |

clipsal.com/iconic