



Automatizarea si controlul mai usoare ca niciodata

Variator de viteza Altivar 310.

Variatoarele de viteza Altivar 310 pentru aplicatii, de la 0.37 la 11kW/ 0.5 la 15HP, sunt potrivite pentru nevoile dumneavoastra. Acestea ofera avantaje precum: accesibilitate in piata, usurinta de utilizare, robustețe și disponibilitate in utilizare.



Potrivit pentru:

- Optimizarea spatiului de instalare
- Optimizarea timpului si a costului
- Economisirea costului de servicii

Conceput cu scopul de a fi:

- Usor de instalat
- Usor de montat si folosit
- Usor de intretinut

Robustețe

- Design robust pentru medii dure
- Protectie si performanta tot mai ridicate

Disponibil mereu

- Gama variata
- Asistenta tehnica la nivel mondial



Masini textile



Masini-unelte



Masini pentru fabricarea lemnului



Manipularea materialelor



Masini de impachetare si imprimare



Masini ceramice

se.com/altivar310

Life Is On

Schneider
Electric

Altivar 310

Caracteristici generale

Gama de putere:
0.37 la 11kW

Gama de putere principala:
380V AC 3-faze 380-460V

- 1: 0.37kW, 0.75kW
- 2: 1.5kW, 2.2kW
- 3: 3kW, 4kW, 5.5kW
- 4: 7.5kW, 11kW

Capacitate de control:

- U/F, control vector, U2/F
- 0 poate fi setat

Control ventilator de racire:

- Controlul temperaturii
- Functionare in sincron

Viteza alocata up/down



Terminal de afisare

Afisaj integrat

- Afisaj cu 4 cifre

Terminal de afisare la distanta (optional)

- Cu capac inchis
- Cu capac deschis: butoane accesibile RUN, FWD/REV, si STOP

Control I/O

Control terminal

- Intrari analogice AI1
- Iesiri analogice AO1
- Iesiri releu: R1A, R1B, R1C
- Intrari logice LI1 to LI4
- Iesiri logice LO+, LO-

Comunicatie:

- Protocol de comunicatie Modbus

Motor	Alimentare			Altivar 310				Referinte
	Curent maxim de intrare		Putere aparenta la U2	Curent de scurtcircuit prezumat Isc	Curent maxim permanent pe iesire (in)	Curentul tranzitoriu maxim pentru 60s	Puterea disipata la curent de iesire maxim (in)	
	la U1	la U2						
kW	A	A	kVA	A	A	A	W	
0.37	1.8	2.1	1.4	2.1	1.5	2.3	19.63	ATV310H037N4E
0.75	3.1	3.5	2.5	3.5	2.3	3.5	28.83	ATV310H075N4E
1.5	5.4	6.5	4.3	6.5	4.1	6.2	51.82	ATV310HU15N4E
2.2	7.2	8.8	5.7	8.8	5.5	8.3	66.82	ATV310HU30N4E
3	9.2	11.1	7.3	11.1	7.1	10.7	80.24	ATV310HU22N4E
4	11.4	13.7	9.1	13.7	9.5	14.3	102.72	ATV310HU30N4E
5.5	14.3	21.3	11.4	21.3	12.6	18.9	141.54	ATV310HU40N4E
7.5	22.4	26.6	17.8	26.6	17	25.5	203.87	ATV310HU55N4E
11	30.4	36.1	24.2	36.1	24	36	294.70	ATV310HU75N4E

se.com/altivar310

Life Is On

Schneider
Electric

Adresa: str. Gara Herăstrău, nr. 4

Clădirea Green Court - A, et. 2

Sector 2, București, cod 020334

Tel: + (40) 21 203 06 60

Fax: + (40) 21 232 15 98

©2019 Schneider Electric. All rights reserved. Life Is On Schneider Electric is a trademark and the property of Schneider Electric SE, its subsidiaries and affiliated companies.
• 998-20624938