



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
JGL36225



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

General Application:	Provides overload and short circuit protection
For Use With:	Industrial Enclosures and Switchboards
Approvals:	UL Listed - CSA Certified - IEC Rated
Mounting Type:	Unit Mount
Terminal Type:	Line: Lug - Load: Lug
Wire Size:	#3/0-350 AWG/kcmil(Al/Cu)
Weight:	5 Pounds
Depth:	5.00 Inches
Height:	7.52 Inches
Width:	4.12 Inches

Specification:

Description:	PowerPact J-frame Thermal Magnetic Circuit Breaker
Number of Poles:	3-Pole
Ampere Rating:	225A
Voltage Rating:	600VAC/250VDC
Interrupting Rating:	65kA at 240VAC - 35kA at 480VAC - 18kA at 600VAC - 20kA at 250VDC
Circuit Breaker Rating:	80% Rated
Fixed AC Magnetic Trip:	Low: 1125A - High: 2250A