


Power Connectors:  
2 x 6.35 mm

Control Connectors:  
1 x 6.35mm or 2 x 2.8mm



**Note:**

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

# LC1D099P7

**Schneider Electric**

Schneider Electric United States  
North American Division  
Boston One Campus  
800 Federal Street  
Andover, MA 01810, USA  
Phone: +1 8773425173  
Email: CCC@us.schneider-electric.com

**Technical Information:**

Rating: 600V / 9A  
 UL File/CCN: E164862 / NLDX  
 CSA File: LR43364 3211 04  
 Meets Standards: IEC 60647-4  
 Weight: 0.71 lb (0.32 kg)  
 Termination Method: Slip-on  
 Wire Size: Power: #14 - #18 AWG  
 Control: #14 - #18 AWG  
 Terminal torque: Power: N/A  
 Control: N/A  
 Mounting Hwd.: 35mm DIN Rail, #8 screw

**Specification:**

Description: TeSys D IEC Contactor - 9A - Vac Coil  
 Type: TeSys D IEC Contactor - 9A - 230Vac Coil  
 Voltages Code: P7 at 230Vac 50/60 Hz

Coil Consumption: Inrush 70 VA  
 Sealed 7.5 VA

Single Phase			Three Phase		
115V	230V	200V	230V	460V	575V
0.5 HP	1 HP	2 HP	2 HP	5 HP	7.5 HP