




Note:
- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

LC1D09Q7



Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone: +1 8773425173
Email: CCC@us.schneider-electric.com

Technical Information:

Rating: 600V / 9A
UL File/CCN: E164862 / NLDX
CSA File: LR43364 3211 04
Meets Standards: IEC 60647-4
Weight: 0.71 lb (0.32 kg)
Termination Method: Screw Clamp
Wire Size: Power: #10 - #18 AWG
Control: #10 - #18 AWG
Terminal torque: Power: 15 lb-in (1.7 Nm)
Control: 15 lb-in (1.7 Nm)
Mounting Hwd.: 35mm DIN Rail, #8 screw

Specification:

Description: TeSys D IEC Contactor - 9A - Vac Coil
Type: TeSys D IEC Contactor - 9A - 380Vac Coil
Voltages Code: Q7 at 380Vac 50/60 Hz

Coil Consumption: Inrush 70 VA
Sealed 7.5 VA

Single Phase			Three Phase		
115V	230V	200V	230V	460V	575V
0.5 HP	1 HP	2 HP	2 HP	5 HP	7.5 HP