



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
LC1D123F7

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Rating: 600V / 12A
 UL File/CCN: E164862 / NLDX
 CSA File: LR43364 3211 04
 Meets Standards: IEC 60647-4
 Weight: 0.72 lb (0.325 kg)
 Termination Method: Spring Clamp
 Wire Size: Power: #14 - #18 AWG
 Control: #14 - #18 AWG
 Terminal torque: Power: N/A
 Control: N/A
 Mounting Hwd.: 35mm DIN Rail, #8 screw

Specification:

Description: TeSys D IEC Contactor - 12A - Vac Coil
 Type: TeSys D IEC Contactor - 12A - 110Vac Coil
 Voltages Code: F7 at 110Vac 50/60 Hz

Coil Consumption: Inrush 70 VA
 Sealed 7.5 VA

Single Phase			Three Phase		
115V	230V	200V	230V	460V	575V
1 HP	2 HP	3 HP	3 HP	7.5 HP	10 HP