


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

LC1D18V7



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Rating: 600V / 18A
 UL File/CCN: E164862 / NLDX
 CSA File: LR43364 3211 04
 Meets Standards: IEC 60647-4
 Weight: 0.73 lb (0.33 kg)
 Termination Method: Screw Clamp
 Wire Size: Power: #10 - #18 AWG
 Control: #10 - #18 AWG
 Terminal torque: Power: 15 lb-in (1.7 Nm)
 Control: 15 lb-in (1.7 Nm)
 Mounting Hwd.: 35mm DIN Rail, #8 screw

Specification:

Description: TeSys D IEC Contactor - 18A - Vac Coil
 Type: TeSys D IEC Contactor - 18A - 400Vac Coil
 Voltages Code: V7 at 400Vac 50/60 Hz

Coil Consumption: Inrush 70 VA
 Sealed 7.5 VA

Single Phase			Three Phase		
115V	230V	200V	230V	460V	575V
1 HP	3 HP	5 HP	5 HP	10 HP	15 HP