



**Note:**  
- Drawings Not To Scale  
- Drawings Subject to Change Without Notice  
- Dimensions are inches next to [Millimeters]

Part No.:

**LC1D32M7**



Schneider Electric United States  
North American Division  
Boston One Campus  
800 Federal Street  
Andover, MA 01810, USA  
Phone: +1 8773425173  
Email: CCC@us.schneider-electric.com

**Technical Information:**

Rating: 600V / 32A  
UL File/CCN: E164862 / NLDX  
CSA File: LR43364 3211 04  
Meets Standards: IEC 60647-4  
Weight: 0.83 lb (0.375 kg)  
Termination Method: Screw Clamp  
Wire Size: Power: #6 - #14 AWG  
Control: #10 - #18 AWG  
Terminal torque: Power: 20 lb-in (2.5 Nm)  
Control: 15 lb-in (1.7 Nm)  
Mounting Hwd.: 35mm DIN Rail, #8 screw

**Specification:**

Description: TeSys D IEC Contactor - 32A - Vac Coil  
Type: TeSys D IEC Contactor - 32A - 220Vac Coil  
Voltages Code: M7 at 220Vac 50/60 Hz

Coil Consumption: Inrush 70 VA  
Sealed 7.5 VA

Single Phase			Three Phase		
115V	230V	200V	230V	460V	575V
2 HP	5 HP	10 HP	10 HP	20 HP	30 HP