



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

LC1D40A3LE7



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Rating: 600V / 40A
 UL File/CCN: E164862 / NLDX
 CSA File: LR43364 3211 04
 Meets Standards: IEC 60647-4
 Weight: 0.85 lb (0.385 kg)
 Termination Method: Spring Clamp
 Wire Size: Power: #2 - #16 AWG
 Control: #12 - #20 AWG
 Terminal torque: Power: 70 lb-in (8 Nm)
 Control: N/A
 Mounting Hwd.: 35mm DIN Rail, #8 screw

Specification:

Description: TeSys D IEC Contactor New Type with Everlink® - 40A - Vac Coil
 Type: TeSys D IEC Contactor - 40A - 208Vac Coil
 Voltages Code: LE7 at 208Vac 50/60 Hz

Coil Consumption: Inrush 140 VA
 Sealed 13 VA

Single Phase		Three Phase			
115V	230V	200V	230V	460V	575V
3 HP	5 HP	10 HP	10 HP	30 HP	30 HP