



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

LC1D806M7



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Rating: 600V / 80A
 UL File/CCN: E164862 / NLDX
 CSA File: LR43364 3211 04
 Meets Standards: IEC 60647-4
 Weight: 1.59 lb (0.72 kg)
 Termination Method: Ring Tongue
 Wire Size: Power: Lug Size 0.62 in (16mm)
 Control: Lug Size 0.32 in (8mm)
 Terminal torque: Power: 54 lb-in (6 Nm)
 Control: 15 lb-in (1.7 Nm)
 Mounting Hwd.: 35mm DIN Rail, #6.5mm Dia

Specification:

Description: TeSys D IEC Contactor - 80A - Vac Coil
 Type: TeSys D IEC Contactor - 80A - 220Vac Coil
 Voltages Code: M7 at 220Vac 50/60 Hz

Coil Consumption: Inrush 245 VA
 Sealed 26 VA

Single Phase		Three Phase			
115V	230V	200V	230V	460V	575V
7.5 HP	15 HP	20 HP	25 HP	60 HP	60 HP