


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

LC1K09013P7



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Rating: 600V / 9A
 UL File/CCN: E164353 / NKCR
 CSA File: LR43364 3211 03
 Meets Standards: IEC 60647-1-1
 Weight: 0.40 lb (0.18 kg)
 Termination Method: Spring Terminal
 Wire Size: Power: #16 - #18 AWG
 Control: #16 - #18 AWG
 Terminal torque: Power: N/A
 Control: N/A
 Mounting Hwd.: 35mm DIN Rail, 4mm screw

Specification:

Description: TeSys K Non-reversing Contactor
 Type: TeSys K IEC Contactor - 9A - 230Vac Coil
 Voltages Code: P7 at 230Vac 50/60 Hz

Coil Consumption: Inrush 30 VA
 Sealed 4.5 VA

Single Phase		Three Phase			
115V	230V	200V	230V	460V	575V
0.5 HP	1.5 HP	2 HP	3 HP	5 HP	5 HP