


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

LP1K1210BD



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Rating: 600V / 12A
 UL File/CCN: E164353 / NKCR
 CSA File: LR43364 3211 03
 Meets Standards: IEC 60647-1-1
 Weight: 0.40 lb (0.18 kg)
 Termination Method: Screw Clamp
 Wire Size: Power: #12 - #18 AWG
 Control: #12 - #18 AWG
 Terminal torque: Power: 7 lb-in (0.8 Nm)
 Control: 7 lb-in (0.8 Nm)
 Mounting Hwd.: 35mm DIN Rail, 4mm screw

Specification:

Description: TeSys K Non-reversing Contactor
 Type: TeSys K IEC Contactor - 12A - 24Vdc Coil
 Voltages Code: BD at 24VDC

Coil Consumption: Inrush 3 W
 Sealed 3W

Single Phase		Three Phase			
115V	230V	200V	230V	460V	575V
0.5 HP	1.5 HP	3 HP	3 HP	7.5 HP	10 HP