


**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**LP4K09013BW3**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

Rating: 600V / 9A  
 UL File/CCN: E164353 / NKCR  
 CSA File: LR43364 3211 03  
 Meets Standards: IEC 60647-1-1  
 Weight: 0.40 lb (0.18 kg)  
 Termination Method: Spring Terminal  
 Wire Size: Power: #16 - #18 AWG  
 Control: #16 - #18 AWG  
 Terminal torque: Power: N/A  
 Control: N/A  
 Mounting Hwd.: 35mm DIN Rail, 4mm screw

**Specification:**

Description: TeSys K Non-reversing Contactor  
 Type: TeSys K IEC Contactor - 9A - 24Vdc Coil  
 Voltages Code: BW3 at 24VDC

Coil Consumption: Inrush 1.8 W  
 Sealed 1.8 W

Single Phase		Three Phase			
115V	230V	200V	230V	460V	575V
0.5 HP	1.5 HP	2 HP	3 HP	5 HP	5 HP