



## Cable ties

Package with Russian, Kazakh, Ukrainian, Latvian, Lithuanian and Estonian



P147785

### + Benefits

- The cable ties are self-locking. They cannot be opened and re-sealed.
- The cable ties have smooth rounded edges for easier handling and safer installation.
- The bent rounded tip allows easier insertion through the head of the cable tie.
- User friendly re-sealable packaging and documented quality.
- Manufactured and tested to EN62275, RoHS compliant.



P147787

### Thorsman cable ties

#### Description

■ Cable ties are used for a wide range of applications including bundle up and fix cables, conduits and tubing

■ Material PA6.6

■ Available in black and clear colour

■ Max operating temperature -40°C to +85°C

■ Minimum installation temperature -20°C.

#### Application

■ There are two types of Thorsman cable ties available:

□ made of clear polyamide, for indoor use

□ made of UV-stabilized black polyamide for both indoor and outdoor use.

#### Thorsman cable ties (x 100)

Type	Length (mm)	Colour	Qty per package	Ref. No.
<b>Thorsman cable ties</b>			<b>Language pack</b>	
2.5 mm	100	Clear	100	IMT46250
	100	Black	100	IMT46251
	120	Clear	100	IMT46252
3.6 mm	120	Black	100	IMT46253
	150	Clear	100	IMT46254
2.5 mm	150	Black	100	IMT46255
	160	Black	100	IMT46256
3.6 mm	160	Clear	100	IMT46257
	200	Black	100	IMT46258
	200	Clear	100	IMT46259
4.8 mm	200	Clear	100	IMT46260
	200	Black	100	IMT46261
4.8 mm	200	Clear	100	IMT46262
	200	Black	100	IMT46263
	250	Clear	100	IMT46264
3.6 mm	250	Black	100	IMT46265
	300	Clear	100	IMT46266
4.8 mm	300	Black	100	IMT46267
	300	Clear	100	IMT46268
7.6 mm	300	Black	100	IMT46269
	300	Black	100	IMT46270
4.8 mm	370	Clear	100	IMT46271
	370	Black	100	IMT46272
7.6 mm	380	Clear	100	IMT46273
	380	Black	100	IMT46274
8.8 mm	550	Black	100	IMT46275
	550	Clear	100	IMT46276
	780	Black	100	IMT46277

#### Thorsman cable ties (x 20)

Type	Length (mm)	Colour	Qty per package	Ref. No.
<b>Thorsman cable ties</b>			<b>Language pack</b>	
2.5 mm	100	Black	20	IMT46131
		Clear	20	IMT46121
4.6 mm	200	Black	20	IMT46132
		Clear	20	IMT46122
4.8 mm	280	Black	20	IMT46133
		Clear	20	IMT46123
	380	Clear	20	IMT46124
		Black	20	IMT46134