



Cable ties Global package



P147785

+ Benefits

- The cable ties are self-locking. They cannot be opened and re-sealed.
- The cable ties have smooth rounded edges for easier handling and safer installation.
- The bent rounded tip allows easier insertion through the head of the cable tie.
- User friendly re-sealable packaging and documented quality.
- Manufactured and tested to EN62275, RoHS compliant.



P147787



P148324



P148323



P148326



P148300

Thorsman cable ties

Description

- Cable ties are used for a wide range of applications including bundle up and fix cables, conduits and tubing
- Material PA6.6
- Available in black and clear colour
- Max operating temperature -40°C to +85°C
- Minimum installation temperature -20°C.

Application

- There are two types of Thorsman cable ties available:
 - made of clear polyamide, for indoor use
 - made of UV-stabilized black polyamide for both indoor and outdoor use.

Thorsman cable ties (x 100)

Type	Length (mm)	Colour	Qty per package	Ref. No.
Thorsman cable ties			No language pack	
2.5 mm	100	Clear	100	IMT46026
		Black	100	IMT46033
	120	Clear	100	IMT46035
		Black	100	IMT46036
	160	Clear	100	IMT46074
		Black	100	IMT46073
200	Clear	100	IMT46158	
	Black	100	IMT46157	
3.6 mm	150	Clear	100	IMT46064
		Black	100	IMT46071
	200	Clear	100	IMT46149
		Black	100	IMT46156
	300	Clear	100	IMT46921
		Black	100	IMT46922
4.8 mm	200	Clear	100	IMT46101
		Black	100	IMT46118
	250	Clear	100	IMT46918
		Black	100	IMT46968
	300	Clear	100	IMT46919
		Black	100	IMT46969
370	Clear	100	IMT46248	
	Black	100	IMT46970	
7.6 mm	300	Black	100	IMT46923
	380	Clear	100	IMT46286
		Black	100	IMT46293
		Clear	100	IMT46926
8.8 mm	550	Clear	100	IMT46924
		Black	100	IMT46927
	780	Black	100	IMT46924

Thorsman cable ties (x 20)

Type	Length (mm)	Colour	Qty per package	Ref. No.
Thorsman cable ties			No language pack	
2.5 mm	100	Black	20	IMT46231
		Clear	20	IMT46221
4.6 mm	200	Black	20	IMT46232
		Clear	20	IMT46222
4.8 mm	280	Black	20	IMT46233
		Clear	20	IMT46223
	380	Clear	20	IMT46224
		Black	20	IMT46234

Thorsman accessories

Type	Colour	Qty per package	Dimensions w/l (mm)	Ref. No.
Self-adhesive bases				
No language pack				
For max. tie width 3.6 mm	Clear	100	19/19/5.8	IMT47000
For max. tie width 4.8 mm	Clear	100	28/28/6.4	IMT47001
Cradle				
For max. tie width 7.8 mm	Clear	100	22/16/9.6	IMT47002
Cable tie with ID tab				
Cable tie with ID tab 100 x 2.5 mm	Clear	100	100/2.5	IMT47004