



Trailing leads

French pin trailing leads



Trailing leads

Description

- Available in 3 or 5 socket outlets selection, with different cable lengths and finishing
- Manufactured from flame retardant PP or PC material
- Operating temperature: -10°C to +40°C
- Switch with neon indicator
- Degree of protection: IP20
- Cable size: 1 mm²
- Rated operational voltage (Ue): 250 V AC
- Rated current (In): 16 A
- Hanger holes
- Outlet poles configuration: 2P+E.



Benefits





Tested and approved to the following standards:

Target market	France, Poland, Finland, Sweden, Spain and Portugal	Russia
Standard	Socket: IEC 60884-2-7 Socket with USB charging: IEC 60884-2-7 EN 60950-1 EN 55022 EN 55024 EN 61000-6-1 EN 61000-6-3	Socket: GOST 30851.1.2.3-2012 Socket with USB charging: GOST 30851.2.3-2012 GOST 30805.14.1-2013 GOST 30805.14.2-2013 GOST 30804.3.2-2013 GOST IEC 61000-3-3-2015

Application

- Suitable for indoor use in everyday household and commercial building.

French trailing leads
















Type	Socket	Cable length (m)	Colour	Dimensions A/B/C (mm)		Qty per package	Ref. No.
French trailing leads							
Selection of 3 and 5 socket outlets in anthracite and white colors, available in 1.5 m, 3 m and 5 m cable lengths. All designed with child-protection shutter and general on/off switch to ensure safety and energy saving. Compliant to NF, BBJ and CE. Material: PP							
3 gang extension cord	3	1.5	White	57/41/206		1	ST9331W
			Anthracite				1
5 gang extension cord	5	1.5	White	57/41/291		1	ST9351W
			Anthracite				1
3 gang extension cord	3	3	White			1	ST9353W
			Anthracite				1

P147613
P147614
P147615
P147616
P147617
P147618





French trailing leads with 2 USB ports




Type	Socket	Cable length (m)	Colour	Dimensions A/B/C (mm)		Qty per package	Ref. No.	
French trailing leads with 2 USB ports								
Selected models are embedded with USB charging ports, which are up to 2.4 A max capacity and suitable for charging tablets (or other electronic devices) at 2.1 A per port. Available in real material finishing extended from existing Schneider wiring devices range Odace. Compliant to NF, BBJ and CE. USB output: 5 V DC, 2.4 A max. Material: PC / PP / Wood / Aluminum.								
 P147578  P147579  P147580  P147514  P147515  P147516  P147517	3 gang extension cord with USB	3	1.5	White	57/41/254	1	ST933U1W	
				Anthracite		1	ST933U1B	
				White/ aluminium brosse		1	ST933U1WA	
				White/ bronze brosse		1	ST933U1WB	
				White/bois nordique		1	ST933U1WC	
				Anthracite/ aluminium brosse		1	ST933U1BA	
				Anthracite/ bronze brosse		1	ST933U1BB	
	 P147524  P147538  P147528  P147527  P147528  P147569  P147570	5 gang extension cord with USB	5	1.5	White	57/41/339	1	ST935U1W
					Anthracite		1	ST935U1B
					White/ aluminium brosse		1	ST935U1WA
				Anthracite/ bronze brosse		1	ST935U1WB	
				White/bois nordique		1	ST935U1WC	
				Anthracite/ aluminium brosse		1	ST933U1BA	
				Anthracite/ bronze brosse		1	ST935U1BB	



Trailing leads

Schuko pin trailing leads
















Schuko trailing leads

Type	Socket	Cable length (m)	Colour	Dimensions A/B/C (mm)		Qty per package	Ref. No.	
Schuko trailing leads								
Selection of 3 and 5 socket outlets in anthracite and white colors, available in 1.5 m, 3 m and 5 m cable lengths. All designed with child-protection shutter and general on/off switch to ensure safety and energy saving. All compliant to CE and selected models certified with SEMKO, FIMKO, AENOR or EAC. Material: PP.								
 P 147619	3	1.5	White	57/41/206		1	ST9431W	
			Anthracite				ST9431B	
	3	3	White			1	ST9433W	
			Anthracite				ST9433B	
	5	5	5	White			1	ST9435W
				Anthracite				ST9435B
 P 147624	5	1.5	White	57/41/291		1	ST9451W *	
			Anthracite				ST9451B *	
	3	3	3	White			1	ST9453W
				Anthracite				ST9453B *
	5	5	5	White			1	ST9455W
				Anthracite				ST9455B *

(*) Not EAC compliant



Schuko trailing leads with 2 USB ports

Type	Socket	Cable length (m)	Colour	Dimensions A/B/C (mm)		Qty per package	Ref. No.	
Schuko trailing leads with 2 USB ports								
Selected models are embedded with USB charging ports, which are up to 2.4 A max capacity and suitable for charging tablets (or other electronic devices) at 2.1 A per port. Available in real material finishing extended from existing Schneider wiring devices range Odace.								
All compliant to CE and selected models certified with SEMKO, FIMKO, AENOR or EAC.								
Output voltage: 5 V DC. Output current: 2.4 A.								
Material: PC / PP / Aluminum.								
	3	1.5	White	57/41/254		1	ST943U1W *	
			Anthracite			1	ST943U1B *	
	3	3	White			1	ST943U3W	
			Anthracite			1	ST943U3B	
	3	3	White/ aluminium brosse			1	ST943U1WA *	
			Anthracite/ aluminium brosse			1	ST943U1BA *	
		5	1.5	White	57/41/291		1	ST945U1W *
				Anthracite			1	ST945U1B *
		5	5	White/ aluminium brosse			1	ST945U1WA *
				Anthracite/ aluminium brosse			1	ST945U1BA *
3		3	White			1	ST945U3W	
			Anthracite			1	ST945U3B *	

(*) Not EAC compliant