



[Link to Worklamp catalogue](#)



## LED work lights

### Description

The Thorsman Led Work Light range has been designed to offer more features and to cover a maximum number of applications thanks to its 6 different sizes.

All products in the range are equipped with the latest Led technology to offer better energy efficiency, higher light quality and a longer lifetime.



### Application

Due to its high IP and IK, it's suitable to any workplace, under any kind of weather condition. Suitable for professional craftsmen. Temperature resistant but "cold light", Thorsman LED lights could be used in any place at any moment.

## + Benefits

- Easy to transport, position and mount. Multi-functional
- Can be used in harsh conditions : designed and approved for heavy use, in and outdoor
- Can be placed, mounted or hung
- Shock-absorbent rubber coating
- Resistant to oil and acid.
- Does not get hot
- Efficient LED technology : ultra long life time
- Patented suspension strap (on Thorsman 30 and 50 LED and 17R LED)
- Socket(s) on the back (Thorsman 30 and 50)
- Rechargeable (Thorsman 17R LED, Thorsman Mini 1.5 and Top view 2.0)



## Range



Thorsman 18 LED	Type	Plug	Power	Lumen	Cable	IP	Weight	Ref. No.
	Thorsman 18 LED - Contour plug	Schuko/Contour	18 W	1500 lm	2 m H05RN-F 2X1.0	IP54	1 kg	IMT33094
	Thorsman 18 LED - Contour plug Nordics	Schuko/Contour	18 W	1500 lm	2 m H05RN-F 2X1.0	IP54	1 kg	IMT33095
	Thorsman 18 LED - CH plug	CH	18 W	1500 lm	2 m H05RN-F 2X1.0	IP54	1 kg	IMT33096
	Thorsman 18 LED - UK plug 240V	UK 240 V	18 W	1500 lm	2 m H05RN-F 2X1.0	IP54	1 kg	IMT33097
	Thorsman 18 LED - UK plug 110V	UK 110 V	18 W	1500 lm	2 m H05RN-F 2X1.0	IP54	1 kg	IMT33098
Thorsman 30 LED	Type	Plug	Power	Lumen	Cable	IP	Weight	Ref. No.
	Thorsman 30 LED - Schuko FR	Schuko FR	30 W	2850 lm	2 m H07RN-F 3X1.5	IP54	1.7 kg	IMT33099
	Thorsman 30 LED - Schuko DE	Schuko DE	30 W	2850 lm	2 m H07RN-F 3X1.5	IP54	1.7 kg	IMT33100
	Thorsman 30 LED - Schuko Nordics	Schuko Nordics	30 W	2850 lm	2 m H07RN-F 3X1.5	IP54	1.7 kg	IMT33101
	Thorsman 30 LED - CH plug	CH	30 W	2850 lm	2 m H07RN-F 3X1.5	IP54	1.7 kg	IMT33102
	Thorsman 30 LED - DK plug	DK	30 W	2850 lm	2 m H07RN-F 3X1.5	IP54	1.7 kg	IMT33103
	Thorsman 30 LED - UK plug 240 V	UK 240 V	30 W	2850 lm	2 m H07RN-F 3X1.5	IP54	1.7 kg	IMT33104
	Thorsman 30 LED - UK plug 110 V	UK 110 V	30 W	2850 lm	2 m H07RN-F 3X1.5	IP44	1.8 kg	IMT33105







[Link to Worklamp catalogue](#)

## Range

Thorsman 50 LED		Type	Plug	Power	Lumen	Cable	IP	Weight	Ref. No.
 	Thorsman 50 LED - Schuko FR	Schuko FR	50 W	4000 lm	3 m H07RN-F 3X1.5	IP54	2.4 kg	<b>IMT33106</b>	
	Thorsman 50 LED - Schuko DE	Schuko DE	50 W	4000 lm	3 m H07RN-F 3X1.5	IP54	2.4 kg	<b>IMT33107</b>	
	Thorsman 50 LED - Schuko Nordics	Schuko Nordics	50 W	4000 lm	3 m H07RN-F 3X1.5	IP54	2.4 kg	<b>IMT33108</b>	
	Thorsman 50 LED - CH plug	CH	50 W	4000 lm	3 m H07RN-F 3X1.5	IP54	2.4 kg	<b>IMT33109</b>	
	Thorsman 50 LED - DK plug	DK	50 W	4000 lm	3 m H07RN-F 3X1.5	IP54	2.4 kg	<b>IMT33110</b>	
	Thorsman 50 LED - UK plug 240 V	UK 240 V	50 W	4000 lm	3 m H07RN-F 3X1.5	IP54	2.4 kg	<b>IMT33111</b>	
	Thorsman 50 LED - UK plug 110 V	UK 110 V	50 W	4000 lm	3 m H07RN-F 3X1.5	IP44	2.5 kg	<b>IMT33112</b>	

Thorsman 25 LED		Type	Plug	Power	Lumen	Cable	IP	Weight	Ref. No.
 	Thorsman 25 LED	DK	25 W	2500 lm	5 m H05RN-F 3X1.0	IP67	1.9 kg	<b>IMT33088</b>	
	Thorsman 25 LED	Schuko/Contour	25 W	2500 lm	5 m H05RN-F 3X1.0	IP67	1.9 kg	<b>IMT33089</b>	



Rechargeable		Type	Plug	Power	Lumen	Cable	IP	Weight	Ref. No.
   	Thorsman 17R LED	Euro Plug	17 W	1500 lm or 750 lm	-	IP54/IK07	1.86 kg	<b>IMT33133</b>	
	Thorsman Mini 1.5 LED - with USB charger		1.5 W	55/110 lm	-	IP65	112 g	<b>IMT33093</b>	
	Thorsman Top-View LED 2.0 LED - with USB charger		2 W	80/160 lm	-	IP65	120 g	<b>IMT33113</b>	

### Accessories

#### Description

Thorsman work lights Tripod has been designed to bring even more flexibility and better light distribution to all projects/applications. To fix 2 work lights, a bracket is available to improve the total light power. Thorsman tripod is suitable for Thorsman 15 LED, 30 LED, 50 LED and 17R LED.

## Range

		Type	Ref. No.
 	Thorsman tripod		<b>IMT33114</b>
	Thorsman Bracket - 2 work lights		<b>IMT33115</b>