



NRNT.E173076 - SWITCHES, INDUSTRIAL CONTROL

Switches, Industrial Control

See General Information for Switches, Industrial Control

SCHNEIDER ELECTRIC INDUSTRIES S A, DBA TELEMECANIQUE

E173076

8001 Knightdale Blvd
Knightdale, NC 27545 USATrademark and/or Tradename:  ,  **Telemecanique** ,  **Telemecanique** ,  , **Investigated to ANSI/UL 508****Control Relay** Model(s) RM22JA21MR, RM22JA31MR, RM22LA32MR, RM22LA32MT, RM22LG11MR, RM22LG11MT, RM22TA31, RM22TA33, RM22TG20, RM22TR31, RM22TR33, RM22TU21, RM22TU23, RM22UA21MR, RM22UA22MR, RM22UA23MR, RM22UA31MR, RM22UA32MR, RM22UA33MR, RM22UA33MT, RM22UB34, RM35JA32MR, RM35JA32MT**Control relays** Model(s) RC8761004, RC8761005, RC8761014, RC8761015, RC8761024, RC8761025, RC8761034, RC8761035, RC8761044, RC8761045, RC87618222, RC87618224, RC87618228, RC87618262, RC87618264, RC87618268, RC87618322, RC87618324, RC87618328, RC87618362, RC87618364, RC87618368, RC87619222, RC87619224, RC87619228, RC87619322, RC87619324, RC87619328, RE8889803, RM17JC00MW, RM17TA00, RM17TE00, RM17TG00, RM17TG20, RM17TT00, RM17TU00, RM17UAS14, RM17UAS15, RM17UAS15315M, RM17UAS16, RM17UB310, RM17UBE15, RM17UBE16, RM35ATL0MW, RM35ATR5MW, RM35ATW5MW, RM35BA10, RM35HZ21FM, RM35JA31MW, RM35JA32MW, RM35LM33MW, RM35LV14MW, RM35S0MW, RM35TF30, RM35TF30SP01, RM35TM250MW, RM35TM50MW, RM35UA11MW, RM35UA12MW, RM35UA13MW, RM35UB330, RM35UB3N30**Electronic timers** Model(s) RE11LABM, RE11LAMW, RE11LCBM, RE11LCMW**Electronic Timers** Model(s) RE22R1ACMR, RE22R1AKMR, RE22R1AMR, RE22R1CMR, RE22R1DMR, RE22R1HMR, RE22R1KMR, RE22R1MAMR, RE22R1MKMR, RE22R1MLMR, RE22R1MYMR, RE22R1QCMU, RE22R1QMQ, RE22R1QMU, RE22R2ACMR, RE22R2AMR, RE22R2AMU, RE22R2CMR, RE22R2DMR, RE22R2HMR, RE22R2KMR, RE22R2MJU, RE22R2MMU, RE22R2MMW, RE22R2MWMR, RE22R2MXMU, RE22R2MYMR, RE22R2QEMR, RE22R2QEMT, RE22R2QGMR, RE22R2QTMR**Electronic timers** Model(s) RE88865100, RE88865105, RE88865180, RE88865185, RE88865300, RE88865305, RE88865380, RE88865385**Electronic Timers** Model(s) RENF22R2MMW**Industrial control, switches, Relay, and Socket** Model(s) RXG11B7 (#), RXG11BD (#), RXG11E7 (#), RXG11ED (#), RXG11F7 (#), RXG11FD (#), RXG11JD (#), RXG11K7 (#), RXG11KD (#), RXG11L7 (#), RXG11M7 (#), RXG11ND (#), RXG11P7 (#), RXG11RD (#), RXG12B7 (#), RXG12BD (#), RXG12E7 (#), RXG12ED (#), RXG12F7 (#), RXG12FD (#), RXG12JD (#), RXG12K7 (#), RXG12KD (#), RXG12L7 (#), RXG12M7 (#), RXG12ND (#), RXG12P7 (#), RXG12RD (#), RXG13B7 (#), RXG13BD (#), RXG13E7 (#), RXG13ED (#), RXG13F7 (#), RXG13FD (#), RXG13JD (#), RXG13K7 (#), RXG13KD (#), RXG13L7 (#), RXG13M7 (#), RXG13ND (#), RXG13P7 (#), RXG13RD (#), RXG15B7 (#), RXG15BD (#), RXG15E7 (#), RXG15ED (#), RXG15F7 (#), RXG15FD (#), RXG15JD (#), RXG15K7 (#), RXG15KD (#), RXG15L7 (#), RXG15M7 (#), RXG15ND (#), RXG15P7 (#), RXG15RD (#), RXG21B7 (#), RXG21BD (#), RXG21E7 (#), RXG21ED (#), RXG21F7 (#), RXG21FD (#), RXG21JD (#), RXG21K7 (#), RXG21KD (#), RXG21L7 (#), RXG21M7 (#), RXG21ND (#), RXG21P7 (#), RXG21RD (#), RXG22B7 (#), RXG22BD (#), RXG22E7 (#), RXG22ED (#), RXG22F7 (#), RXG22FD (#), RXG22JD (#), RXG22K7 (#), RXG22KD (#), RXG22L7 (#), RXG22M7 (#), RXG22ND (#), RXG22P7 (#), RXG22RD (#), RXG23B7 (#), RXG23BD (#), RXG23E7 (#), RXG23ED (#), RXG23F7 (#), RXG23FD (#), RXG23JD (#), RXG23K7 (#), RXG23KD (#), RXG23L7 (#), RXG23M7 (#), RXG23ND (#), RXG23P7 (#), RXG23RD (#), RXG25B7 (#), RXG25BD (#), RXG25E7 (#), RXG25ED (#), RXG25F7 (#), RXG25FD (#), RXG25JD (#), RXG25K7 (#), RXG25KD (#), RXG25L7 (#), RXG25M7 (#), RXG25ND (#), RXG25P7 (#), RXG25RD (#)**Open Type, Electronic Timers** Model(s) RE17LAMW, RE17LCBM, RE17LHBM, RE17LLBM, RE17LMBM, RE17RAMU, RE17RBMU, RE17RCMU, RE17RHMU, RE17RLJU, RE17RLMU, RE17RMEMU, RE17RMJU, RE17RMMU, RE17RMMW, RE17RMMWS, RE17RMXMU**Time delay switches** Model(s) XB5DTB22, XB5DTB23, XB5DTB24, XB5DTB25, XB5DTGM2, XB5DTGM3, XB5DTGM4, XB5DTGM5**Voltage Control Relay** Model(s) RMNF22TB30

(#) - Model mating with Socket models RGZ E1S35M, RGZ E1S48M

Last Updated on 2019-03-01

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2019 UL LLC"