

| | |
|--|--|
| Product | Electronic control unit for luminaires |
| Applicant | Schneider Electric Industries SAS 35, rue Joseph Monier FR 92500 Rueil-Malmaison France |
| Manufacturer | Schneider Electric Industries SAS 35, rue Joseph Monier FR 92500 Rueil-Malmaison France |
| Factory | Enics Eesti AS Valga mnt. 7A 61504 Elva Estonia |
| Ratings | 230V AC, 4-400VA |
| Trade mark |  |
| Model / Type Ref. | SBD200LED |
| Principal characteristics | IP20, IP44 (with special Exxact cover, frame and gasket), Pattern No.: 6. Electronic dimmer for flush mounting. Screw type terminals. μ - gap disconnection. For loads: Incandescent lamps (4-400W). Halogen lamps (4-400W) Electronic step down converters for low voltage halogen lamps (4-400VA). Iron core transformers for low voltage halogen lamps (4-400VA). Dimmable LED lamps (RC mode: 4-200VA, RL LED mode: 4-40VA). |
| A sample of the product was tested and found to be in conformity with | INST EN 60669-1:1999;A1;A2 EN 60669-2-1:2004;A1;A12 |
| Validity | This certificate documents conformity with the standards shown, and also applies as license for use of Nemkos name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation. New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary. |
| Additional information | See page 2 |
| Additional model(s) | No additional models |

Date of issue 02-11-2020



Sweet Yuan

Certification Department

Nemko AS

Philip Pedersens vei 11, 1366 Lysaker, Norway

TEL +47 22 96 03 30 EMAIL info@nemko.com

ENTERPRISE NUMBER NO974404532

Additional information

| Cover design | Center button/ cover | IP20 Frames | IP44 Frames |
|------------------------|-------------------------|--|--|
| Trend | 100949 | 100520 | - |
| Trend Solid | 100949 | 101543 (plastic, glass, metallic) | - |
| Renova/Arezzo | 101368 | 101370 | - |
| Artic | 13620 | 13601 | - |
| Artic Decor | 13620 | 13806 (plastic, glass, metallic) | - |
| Senso | 20005157 | 20005048+20005050 | - |
| Fashion | 227010-0-1 | 224100-0-1 | - |
| Riva | 227010-0-1 | 204120-0-1 | - |
| Scala | 227010-0-1 | 21169.70-0:1 | - |
| Novia | 100634 | 100600, ring: 21179.50-0:2 | - |
| Classic | 227010-0-1 | 21169.151-0:1 | - |
| Joy | 267010-0-1 | 264100-0-1 | - |
| M-Plan II | 5699 | 4881 | - |
| M-Plan | 5699 | 4861 | - |
| M-Plan metal | 5699 | 4751 | - |
| M-Plan real glass | 5699 | 4891 | - |
| M-Arc | 5699 | 4851 | - |
| M-Star | 5699 | 4871 | - |
| Atelier-M | 5699 | 3881 | - |
| 1-M | 5699 | 3891 | - |
| M-Smart | 5699 | 4841 | - |
| M-Creative | BBV35736 | 4010-35 | - |
| Elegance | 5699 | 4021, 4031, 4041, 4051 | - |
| M-Pure/M-Pure Decor | 5699 | 4010-36 | - |
| Artec | 5720 | 4811 (plastic, glass, metallic) | - |
| Antik | 5720 | 4831 (plastic, metallic) | - |
| Tracent | 5720 | 4821 | - |
| D-Life | NHA5193102 | NHA2920502, NHA2923102, NHA2922102 | - |
| Forum | 13620 | W450104 | - |
| Duet | Not specified | Not specified | - |
| Wessen 59 | Not specified | Not specified | - |
| Odace | BBV4007302 | S520702X, S520802X | - |
| Asfora | 300802-xx, 300801-xx | 300101-xx | - |
| Sedna | 100821/100822 | 100101 | - |
| Unica | 2004912 | 6.002 | - |
| Exxact | BBV39712 | Combi (BBV49575), Basic (BBV49550), Primo (BBV49558 or BBV49583), Solid (BBV49558), Solid Glass (S1A45091) | Primo (BBV49583) frame combined with gasket (BBV49557) |

Date of issue 02-11-2020



Sweet Yuan

Certification Department

Nemko AS

 Philip Pedersens vei 11, 1366 Lysaker, Norway
 TEL +47 22 96 03 30 EMAIL info@nemko.com
 ENTERPRISE NUMBER NO974404532