

Product	Electronic dimmer
Applicant	Schneider Electric Industries SAS 35, rue Joseph Monier 92500 Rueil-Malmaison France
Manufacturer	Schneider Electric Industries SAS 35, rue Joseph Monier 92500 Rueil-Malmaison France
Factory	Enics Eesti AS Valga mnt. 7 A 61504 Elva Estonia
Ratings	230V AC; 20 - 315W
Trade mark	
Model / Type Ref.	315GLE
Principal characteristics	IP20, IP44 (with special Exxact cover, frame and gasket); Pattern no.: 6. Electronic dimmer for flush mounting. Screw type terminals. μ - gap disconnection.
A sample of the product was tested and found to be in conformity with	INST EN 60669-1:1999;A1;A2 EN 60669-2-1:2004;A1;A12
Validity	This certificate documents conformity with the standards shown, and also applies as license for use of Nemkos name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation. New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary.
Additional information	See page 3
Additional model(s)	(7) See page 2

Date of issue 25-11-2020




Sweet Yuan
Certification Department


Nemko AS


Philip Pedersens vei 11, 1366 Lysaker, Norway
TEL +47 22 96 03 30 EMAIL info@nemko.com
ENTERPRISE NUMBER NO974404532

Additional model(s)

Product Electronic dimmer
Pos. No 1
Model / Type Ref. 630GLE
Trade mark (if different from page 1)
Rating 230V AC; 20 - 630W
Principal characteristics IP20, IP44 (with special Exxact cover, frame and gasket). Pattern No.:
6. Electronic dimmer for flush mounting. Screw type terminals. μ - gap
disconnection.

Product Electronic dimmer
Pos. No 2
Model / Type Ref. SBD315RC
Trade mark (if different from page 1)

Rating 230V AC, 20 - 315W
Principal characteristics IP20, IP44 (with special Exxact cover, frame and gasket). Pattern No.:
6. Electronic dimmer for flush mounting. Screw type terminals. μ - gap
disconnection.

Product Electronic dimmer
Pos. No 3
Model / Type Ref. SBD630RC
Trade mark (if different from page 1)

Rating 230V AC, 20 - 630W
Principal characteristics IP20, IP44 (with special Exxact cover, frame and gasket). Pattern no.:
6. Electronic dimmer for flush mounting. Screw type terminals. μ - gap
disconnection.

Product Electronic dimmer
Pos. No 4
Model / Type Ref. SBD400R-1
Trade mark (if different from page 1)

Rating 230V AC, 40 - 400W
Principal characteristics IP20, IP44 (with special Exxact cover, frame and gasket). Pattern No.:
1. Electronic dimmer for flush mounting. Screw type terminals. μ - gap
disconnection.

Date of issue 25-11-2020



Sweet Yuan

Certification Department

Nemko AS

Philip Pedersens vei 11, 1366 Lysaker, Norway
TEL +47 22 96 03 30 EMAIL info@nemko.com
ENTERPRISE NUMBER NO974404532

Product
Pos. No
Model / Type Ref.
Trade mark (if different from page 1)

Electronic dimmer
5
SBD400R-2



Rating
Principal characteristics

230V AC, 40 - 400W,
IP20, IP44 (with special Exxact cover, frame and gasket). Pattern No.
6. Electronic dimmer for flush mounting. Screw type terminals. μ - gap
disconnection.

Product
Pos. No
Model / Type Ref.
Trade mark (if different from page 1)

Electronic dimmer
6
SBD400RL



Rating
Principal characteristics

230V AC, 40 - 400W
IP20, IP44 (with special Exxact cover, frame and gasket). Pattern No.:
1. Electronic dimmer for flush mounting. Screw type terminals. μ - gap
disconnection.

Product
Pos. No
Model / Type Ref.
Trade mark (if different from page 1)









Electronic dimmer
7
SBD600RL



Rating
Principal characteristics

230V AC, 40 - 600W
IP20, IP44 (with special Exxact cover, frame and gasket). Pattern No.:
6. Electronic dimmer for flush mounting. Screw type terminals. μ - gap
disconnection.

Additional information

Type ref.	Incandescent (W)	Electronic step-down converter (VA)	Iron-core transformer (VA)	Pattern	Brand
315GLE	20 - 315	20 - 315	-	6	
630GLE	20 - 630	20 - 630	-	6	
SBD315RC	20 - 315	20 - 315	-	6	
SBD630RC	20 - 630	20 - 630	-	6	
SBD400R-1	40 - 400	-	-	1	
SBD400R-2	40 - 400	-	-	6	
SBD400RL	40 - 400	-	40 - 400	6	
SBD600RL	40 - 600	-	40 - 600	6	


Date of issue 25-11-2020



Sweet Yuan
Certification Department

Nemko AS

Philip Pedersens vei 11, 1366 Lysaker, Norway
TEL +47 22 96 03 30 EMAIL info@nemko.com
ENTERPRISE NUMBER NO974404532

Cover design	Center button/ cover	Frames (all 1-5 gang)	Brand
RS 16	L3034	L571	
Elko Plus	L3303	L3295+L3291	
Trend	100949	100520	
Trend Solid	100949	101543 (plastic, glass, metallic)	
Renova/Arezzo	101368	101370	
Artic	13620	13601	
Artic Décor	13620	13806 (plastic, glass, metallic)	
Senso	20005157	20005048+20005050	
Fashion	227010-0-1	224100-0-1	
Riva	227010-0-1	204120-0-1	
Scala	227010-0-1	21169.70-0:1	
Novia	100634	100600, ring: 21179.50-0:2	
Classic	227010-0-1	21169.151-0:1	
Joy	267010-0-1	264100-0-1	
M-Plan II	5699	4881	
M-Plan	5699	4861	
M-Plan metal	5699	4751	
M-Plan real glass	5699	4891	
M-Arc	5699	4851	
M-Star	5699	4871	
Atelier-M	5699	3881	
1-M	5699	3891	
M-Smart	5699	4841	
M-Creative	BBV35736	4010-35	
Elegance	5699	4021, 4031, 4041, 4051	
M-Pure/M-Pure Décor	5699	4010-36	
Artec	5720	4811 (plastic, glass, metallic)	
Antik	5720	4831 (plastic, metallic)	
Tracent	5720	4821	
D-Life	NHA5193102	NHA2920502, NHA2923102, NHA2922102	
Forum	13620	W450104	
Duet	Not specified	Not specified	
Wessen 59	Not specified	Not specified	
Odace	BBV4007302	S520702X, S520802X, S5X0802X	
Asfora	300802-xx, 300801-xx	300101-xx	
Sedna	100821/100822	100101	
Unica	2004912	6.002.---	-
Exxact	BBV39712	Combi (BBV49575), Basic (BBV49550), Primo (BBV49558 or BBV49583), Solid (BBV49558), Solid Glass (S1A45091)	
Exxact Primo	BBV39712	Primo (BBV49583) frame combined with gasket (BBV49557)	
Exxact Basic	BBV39712	Basic (BBV49550) frame combined with gasket (BBV49557)	

Date of issue 25-11-2020



Sweet Yuan

Certification Department

Nemko AS

Philip Pedersens vei 11, 1366 Lysaker, Norway

TEL +47 22 96 03 30 EMAIL info@nemko.com

ENTERPRISE NUMBER NO974404532