

Applicant	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92500 Rueil-Malmaison France
Manufacturer	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92500 Rueil-Malmaison France
Factory	Merten GmbH Fritz-Kotz-Strasse 8 DE-51674 Wiehl Germany
Project Number	PRJ0061035
Product	Socket-outlet
Model/Type Ref.	230/***
Ratings	16A 250V~
Brandname / Trademark	Schneider Electric
Principal Characteristics	Flush type socket-outlet. One-fold, 2P+E, with screwless terminals. With and without shutters. Standard sheet III, IP20, IP21, IP44 (***) in the type designation can be any character or blank to indicate shipping destination and/or enclosure color, not related to product safety).
A sample of the product was tested and found to be in conformity with	Safety IEC 60884-1:2002, IEC 60884-1:2002/AMD1:2006, IEC 60884-1:2002/AMD2:2013 NEK 502:2016/AMD1:2022
Validity	<i>This certificate documents conformity with the standards shown, and also applies as license for use of Nemko's name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation.</i> <i>New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary.</i>
Additional Information	See next pages
Additional model(s)	No additional models

Signature



Jiyea Gim
Certification department

Date of Issue

2024-06-26

Working for a more sustainable future
Please do not print



www.nemko.com

Additional Information

Socket-outlet type list:

Antivandalism: (1-gang)

230/S1B7217902

System M-Creativ

230/2300-35

System M (Thermo/Duro)

230/2371, 230/2373, 230/2376, 230/2374, 230/2300, 230/2301, 230/2309 with or without LED light module Mxx2003-0004, 230/2474, 230/2485, 230/2496, 230/2470, 230/2471, 230/2472, 230/2473, 230/2315, 230/2334 with LED light module Mxx2334

System Design (Thermo/Duro)

230/2375, 230/2377, 230/2372, 230/2379 with or without LED light module Mxx2003-0004, 230/2378, 230/2306, 230/2308, 230/2478, 230/2476, 230/2477

System Design (Thermo/Metal)

230/NHA5191702, 230/NHA5200102, 230/NHA2922902, 230/NHA2922002, 230/NHA5191902, 230/NHA5191802, 230/NHA5195702, 230/NHA5191902, 230/NHA5195702/PHA8168102, 230/NHA5195702/NHA5200202, 230/NHA2920902

AQUADESIGN

230/2330, 230/2335

Renova

230/EAV54699

Frame types:

System M (Thermo+Duro)

M-Smart: (1 - 5 gang) 4841, 4842, 4843, 4844, 4845

1M: (1 - 5 gang)

3891, 3892, 3893, 3894, 3895

M-Plan II: (1 - 3 gang)

4881, 5124, 4882, 5125, 4883, 5126

M-Plan: (1 - 5 gang)

4861, 4862, 4863, 4864, 4865

M-Plan Metall: (1 - 5 gang)

4751, 4752, 4753, 4754, 4755

M-Plan real glas: (1 - 5 gang)

4891, 4892, 4893, 4894, 4895

M-Plan real wood: (1-5 gang)

4051, 4052, 4053, 4054, 4055

Atelier-M: (1 - 5 gang)

3881, 3882, 3883, 3884, 3885

System M - Elegance: (1 - 5 gang)

4021, 4022, 4023, 4024, 4025, 4031, 4032, 4033, 4034, 4035

4041, 4042, 4043, 4044, 4045, 4051, 4052, 4053, 4054, 4055

System M - Exxact (Thermo) Basic: (1 - 5 gang)

BBV49550, BBV49551, BBV49552, BBV49553, BBV49554

Design: (1 - 3 gang)

BBV49558, BBV49559, BBV49561

Solid: (1 - 4 gang)

BBV49558, BBV49559, BBV49561, BBV49589

Solid Glass: (1 - 4 gang)

S1A45091, S1A45092, S1A45094, S1A45092

Combi: (1 - 5 gang)

BBV49575, BBV49576, BBV49577, BBV49578, BBV49580

Primo: (1 - 6 gang)

BBV49583, BBV49584, BBV49587, BBV49585, BBV49586, BBV54904, BBV54905

Gasket for all IP44 frames: (1 - 3 gang)

BBV49557, S1A33102, S1A33103

System M - Creative (1 - 5 gang)

4010-35, 4020-35, 4030-35, 4040-35, 4050-35, 4025-35, 4035-35

System Design (Thermo + Duro)

ARTEC, Antik, Fläche: (1 - 5 gang)

4811, 4812, 4813, 4814, 4815, 4831, 3981, 3982, 3983, 3984, 3985

System M - M-Pure (1 - 5 gang)

4010-36, 4020-36, 4030-36, 4040-36, 4050-36

Signature



Jiyea Gim

Certification department

2024-06-26

Working for a more sustainable future
Please do not print



www.nemko.com

Additional Information

System Design (Thermo + metal + glas/stone)

D-Life (1 - 5 gang)

NHA2920502, NHA2920602, NHA5191402, NHA5191602, NHA2920702

D-Life metal (1 - 5 gang)

NHA2923102, 2xNHA2923302, 2xNHA2923302/1xNHA2923502,
2xNHA2923302/2xNHA2923502, 2xNHA2923302/3xNHA2923502

D-Life glas/basalt (1 - 5 gang)

NHA2922102, NHA2922402, NHA5195402, NHA5195502, NHA2922702

AQUADESIGN: (1 - 4 gang)

4011, 4012, 4013, 4014

Antivandalism (1 - 3 gang)

4801, 4802, 4803

Renova

Glass frame: (1 - 3 gang)

BBV28342, BBV28343, BBV28344

Plastic frame: (1 - 5 gang)

101370, 101371, 101372

Anti Vandalism: (1-gang)

S1B7217902

	Robust Screwless (230/***) Socket Outlets, IK class IK09.			Robust: frame
	Insert	Center Cover	Center Cover Adapter	
Without Shutters	230/***	101363	101599	101600 (1-gang)
With Shutters		EAV54699		

Trend Screwless (230/***) Socket Outlets		
Insert	Center Cover (with Shutters)	Frames
230	NVE66783	100520 (1-gang) 100521 (2-gang) 100522 (3-gang) 100523 (4-gang) 101524 (5-gang)

Signature

Jiyea Gim

Jiyea Gim

Certification department

Date of Issue

2024-06-26

*Working for a more sustainable future
Please do not print*



www.nemko.com