

Applicant	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92500 Rueil-Malmaison France
Manufacturer	Schneider Electric Industries SAS 35, rue Joseph Monier FR 92500 Rueil-Malmaison France
Factory	Merten GmbH Fritz-Kotz-Strasse 8 DE-51674 Wiehl Germany
Project Number	PRJ0061035
Product	Socket-outlet
Model/Type Ref.	270/***
Ratings	16A 250V AC
Brandname / Trademark	
Principal Characteristics	2P+E. One-fold flush-type fixed socket-outlet. With screw terminals. Screw- or claw fixing*. Available with- or without shutters**. IP 20, IP21, IP44, Standard sheet III. *) Socket-outlets with claw fixing are not certified for use in Norway. **) Socket-outlets without shutters are not certified for use in Norway. ("***" in the type designation can be any character or blank to indicate shipping destination and/or enclosure color, not related to product safety).
A sample of the product was tested and found to be in conformity with	Safety IEC 60884-1:2002, IEC 60884-1:2002/AMD1:2006, IEC 60884-1:2002/AMD2:2013 NEK 502:2016/AMD1:2022
Validity	<i>This certificate documents conformity with the standards shown, and also applies as license for use of Nemko's name and certification mark. The certificate and license is valid as long as the applicable conditions are complied with, and provided that any changes to the product are notified to Nemko for acceptance prior to implementation.</i> <i>New standards or amendments to the standards may imply that the product design must be updated and/or that re-testing and re-certification is necessary.</i>
Additional Information	See next pages
Additional model(s)	No additional models

Signature



Jiyea Gim
Certification department

Date of Issue

2024-06-26

*Working for a more sustainable future
Please do not print*



www.nemko.com

Appendix

Socket-outlet type list:

Antivandalism: (1-gang)
270/S1B7217902
System M-Creativ
270/2300-35
System M (Thermo/Duro)
270/2371, 270/2373, 270/2376, 270/2374, 270/2300, 270/2301, 270/2309 with or without LED light module 2003, 270/2474, 270/2485, 270/2496, 270/2470, 270/2471, 270/2472, 270/2473, 270/2334 with LED light module 2334
System Design (Thermo/Duro)
270/2375, 270/2377, 270/2372, 270/2379 with or without LED light module 2003, 270/2378, 270/2306, 270/2308, 270/2478, 270/2476, 270/2477
System Design (Thermo/Metal)
270/NHA2920902, 270/NHA2922002, 270/NHA5195702
AQUADESIGN
270/2330, 270/2335
Renova
270/EAV54699

Frame types:

System M: (Thermo+Duro)
M-Smart: (1 - 5 gang)
4841, 4842, 4843, 4844, 4845
1M: (1 - 5 gang)
3891, 3892, 3893, 3894, 3895
M-Plan II: (1 - 3 gang)
4881, 5124, 4882, 5125, 4883, 5126
M-Plan: (1 - 5 gang)
4861, 4862, 4863, 4864, 4865
M-Plan Metall: (1 - 5 gang)
4751, 4752, 4753, 4754, 4755
M-Plan real glas: (1 - 5 gang)
4891, 4892, 4893, 4894, 4895
M Plan real wood: (1 - 5 gang)
4051, 4052, 4053, 4054, 4055
Atelier-M: (1 - 5 gang)
3881, 3882, 3883, 3884, 3885
System M - Elegance: (1 - 5 gang)
4021, 4022, 4023, 4024, 4025, 4031, 4032, 4033, 4034, 4035
4041, 4042, 4043, 4044, 4045, 4051, 4052, 4053, 4054, 4055
System M - Exxact: (Thermo) Basic: (1 - 5 gang)
BBV49550, BBV49551, BBV49552, BBV49553, BBV49554
Design: (1 - 3 gang)
BBV49558, BBV49559, BBV49561
Solid: (1 - 4 gang)
BBV49558, BBV49559, BBV49561, BBV49589
Solid Glass: (1 - 4 gang)
S1A45091, S1A45092, S1A45094, S1A45092
Combi: (1 - 5 gang)
BBV49575, BBV49576, BBV49577, BBV49578, BBV49580
Primo: (1 - 6 gang)
BBV49583, BBV49584, BBV49587, BBV49585, BBV49586, BBV54904, BBV54905
Gasket for all IP44 frames: (1 - 3 gang)
BBV49557, S1A33102, S1A33103
System M - Creativ: (1 - 5 gang)
4010-35, 4020-35, 4030-35, 4040-35, 4050-35, 4025-35, 4035-35
System M - M Pure: (1 - 5 gang)
4010 36, 4020 36, 4030 36, 4040 36, 4050 36

Signature



Jiyea Gim

Certification department

2024-06-26

*Working for a more sustainable future
Please do not print*



www.nemko.com

Date of Issue

System Design: (Thermo + Duro)
 ARTEC, Antik, Fläche: (1 - 5 gang)
 4811, 4812, 4813, 4814, 4815, 4831, 3981, 3982, 3983, 3984, 3985
 System Design: (Thermo + metal + glas/stone)
 D Life: (1 - 5 gang)
 NHA2920502, NHA2920602, NHA5191402, NHA5191602, NHA2920702
 D Life metal: (1 - 5 gang)
 NHA2923102, 2xNHA2923302, 2xNHA2923302/1xNHA2923502,
 2xNHA2923302/2xNHA2923502, 2xNHA2923302/3xNHA2923502
 D Life glas/basalt: (1 - 5 gang)
 NHA2922102, NHA2922402, NHA5195402, NHA5195502, NHA2922702
 AQUADESIGN: (1 - 4 gang)
 4011, 4012, 4013, 4014
 Antivandalism: (1 - 3 gang)
 4801, 4802, 4803
 Renova
 Glass frame: (1 - 3 gang)
 BBV28342, BBV28343, BBV28344
 Plastic frame: (1 - 5 gang)
 101370, 101371, 101372

Robust Screw-Type (270/****) Socket Outlets, IK class IK09.			Robust: frame
Insert	Center Cover	Center Cover Adapter	
Without Shutters	270/****	101363	101600 (1-gang)
With Shutters		EAV54699	

Trend Screw-Type (270/****) Socket Outlets		
Insert	Center Cover (with Shutters)	Frames
270	NVE66783	100520 (1-gang) 100521 (2-gang) 100522 (3-gang) 100523 (4-gang) 101524 (5-gang)

Signature

Jiyea Gim

Jiyea Gim

Certification department

2024-06-26

Working for a more sustainable future
Please do not print



www.nemko.com

Date of Issue