



NOTES:
1) IP20 TYPE ENCLOSURE
2) AMBIENT TEMP 0-45 C
3) ALTITUDE 1000 m (3300 ft)
4) HUMIDITY 95% NON-CONDENSING
5) MINIMUM CLEARANCES 200 mm TOP AND BOTTOM

	Scale: 0.125	Tolerancing Standard : ISO8015		Units of measure : mm	
	PCSN060Y4R19E ACCUSINE PCSN 60A 208-415V PH+N RACK EXP				
	Number: QGH4799101			Revision: 00	Sheet: 1/1
<p>SQUARE D/SCHNEIDER ELECTRIC HAS PROPRIETARY RIGHTS TO THE INFORMATION CONTAINED HEREON. THIS INFORMATION REMAINS THE PROPERTY OF SQUARE D/SCHNEIDER ELECTRIC AND MAY BE REPRODUCED OR USED ONLY IN ACCORDANCE WITH INSTRUCTIONS OR PERMISSION FROM SQUARE D/SCHNEIDER ELECTRIC. THIS DOCUMENT SHALL BE RETURNED TO SQUARE D/SCHNEIDER ELECTRIC UPON REQUEST. USER SHOULD VERIFY DRAWINGS ARE THE MOST RECENT VERSION PRIOR TO USE.</p> <p>© 2009 Schneider Electric, All Rights Reserved</p>			<p>State:</p> <p>Released for Manufacturing Printed on 2018/06/08</p>		