





16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1

J
I
H
G
F
E
D
C
B
A

J
I
H
G
F
E
D
C
B
A



- NOTES:
 1) IP20 TYPE ENCLOSURE
 2) AMBIENT TEMP 0-45 C
 3) ALTITUDE 1000 m (3300 ft)
 4) HUMIDITY 95% NON-CONDENSING
 5) MINIMUM CLEARANCES 200 mm TOP AND BOTTOM

QGH47989 ACCUSINE PCSN 30A 208-415V PH+N RACK MOD PCSN030Y4R19
 QGH47990 ACCUSINE PCSN 60A 208-415V PH+N RACK MOD PCSN060Y4R19

	Scale: 0.125 Tolerancing Standard : ISO8015 Units of measure : mm
	ACCUSINE PCSN RACK MASTER ACCUSINE PCSN RACK MASTER Number: PHA2996500 Revision: 00 Sheet: 1/1
SQUARE D/SCHNEIDER ELECTRIC HAS PROPRIETARY RIGHTS TO THE INFORMATION CONTAINED HEREON. THIS INFORMATION REMAINS THE PROPERTY OF SQUARE D/SCHNEIDER ELECTRIC AND MAY BE REPRODUCED OR USED ONLY IN ACCORDANCE WITH INSTRUCTIONS OR PERMISSION FROM SQUARE D/SCHNEIDER ELECTRIC. THIS DOCUMENT SHALL BE RETURNED TO SQUARE D/SCHNEIDER ELECTRIC UPON REQUEST. USER SHOULD VERIFY DRAWINGS ARE THE MOST RECENT VERSION PRIOR TO USE. © 2009 Schneider Electric, All Rights Reserved	
State: Released for Manufacturing Printed on 2018/06/08	

16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1

ANY PRINTED COPY OF THIS DOCUMENT USED WITHIN SCHNEIDER ELECTRIC IS CONSIDERED UNCONTROLLED.

PRINTS