



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

PJL36080U43A



by **Schneider Electric**

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

General Application:	Provides overload and short circuit protection
For Use With:	Panelboards and Switchboards
Approvals:	UL Listed - CSA Certified - IEC Rated
Mounting Type:	Unit Mount
Terminal Type:	Lugs (ON and OFF ends)
Wire Size:	#3/0-500 AWG/kcmil(Al/Cu)
Weight:	32 Pounds
Depth:	8.07 Inches
Height:	12.86 Inches
Width:	8.27 Inches

Description:	PowerPact P-frame Electronic Trip Circuit Breaker
Number of Poles:	3-Pole
Sensor Rating:	800A
Voltage Rating:	600VAC
Interrupting Rating:	100kA at 240VAC - 65kA at 480VAC - 25kA at 600VAC
Circuit Breaker Rating:	80% Rated
Electronic Trip Unit:	Micrologic Ammeter Trip Unit (5.0A)
Trip Function:	LSI
Installed Rating Plug:	Type A
Rating Plug Range:	0.4A to 1A

Specification: