



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:  
**PJL36100U44A**

**SQUARE D**  
 by **Schneider Electric**  
 Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**  
 General Application: Provides overload and short circuit protection  
 For Use With: Panelboards and Switchboards  
 Approvals: UL Listed - CSA Certified - IEC Rated  
 Mounting Type: Unit Mount  
 Terminal Type: Lugs (ON and OFF ends)  
 Wire Size: #3/0-500 AWG/kcmil(Al/Cu)  
 Weight: 32 Pounds  
 Depth: 8.07 Inches  
 Height: 16.26 Inches  
 Width: 8.27 Inches

**Specification:**  
 Description: PowerPact P-frame Electronic Trip Circuit Breaker  
 Number of Poles: 3-Pole  
 Sensor Rating: 1000A  
 Voltage Rating: 600VAC  
 Interrupting Rating: 100kA at 240VAC - 65kA at 480VAC - 25kA at 600VAC  
 Circuit Breaker Rating: 80% Rated  
 Electronic Trip Unit: Micrologic Ammeter Trip Unit (6.0A)  
 Trip Function: LSIG  
 Installed Rating Plug: Type A  
 Rating Plug Range: 0.4A to 1A