



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

PKL36080



by **Schneider Electric**

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

General Application: Provides overload and short circuit protection
For Use With: Panelboards and Switchboards
Approvals: UL Listed - CSA Certified - IEC Rated
Mounting Type: Unit Mount
Terminal Type: Lugs (ON and OFF ends)
Wire Size: #3/0-500 AWG/kcmil(Al/Cu)
Weight:
Depth: 8.07 Inches
Height: 12.86 Inches
Width: 8.27 Inches

Description: PowerPact P-frame Electronic Trip Circuit Breaker
Number of Poles: 3-Pole
Sensor Rating: 800A
Voltage Rating: 600VAC
Interrupting Rating: 65kA at 240VAC - 50kA at 480/600VAC
Circuit Breaker Rating: 80% Rated
Electronic Trip Unit: Basic (ET1.0I)
Trip Function: Fixed Long-Time Adjustable Instantaneous Trip
Installed Rating Plug:
Rating Plug Range:

Specification: