



CATALOG NUMBER	A		B		C	
	IN	MM	IN	MM	IN	MM
NC50VS	50.12	1273	27.24	692	10.82	275
NC56VS	56.12	1425	33.24	844	13.82	351
NC62VS	62.12	1578	39.24	997	16.82	427
NC68VS	68.12	1730	45.24	1149	19.82	503
NC74VS	74.12	1883	51.24	1301	22.82	580
NC80VS	80.12	2035	57.24	1454	25.82	656
NC50VF	51.52	1309	27.24	692	10.82	275
NC56VF	57.52	1461	33.24	844	13.82	351
NC62VF	63.52	1613	39.24	997	16.82	427
NC68VF	69.52	1766	45.24	1149	19.82	503
NC74VF	75.52	1918	51.24	1301	22.82	580
NC80VF	81.52	2071	57.24	1454	25.82	656
NC86VS	86.12	2187	63.24	1606	28.82	732
NC86VF	87.52	2223	63.24	1606	28.82	732
NC44VS	44.12	1121	21.24	539	7.82	199
NC44VF	45.52	1131	21.24	539	7.82	199
NC44VSL3R3	44.12	1121	21.24	539	7.82	199
NC50VSL3R3	50.12	1273	27.24	692	10.82	275
NC56VSL3R3	56.12	1425	33.24	844	13.82	351
NC62VSL3R3	62.12	1578	39.24	997	16.82	427
NC68VSL3R3	68.12	1730	45.24	1149	19.82	503
NC74VSL3R3	74.12	1883	51.24	1301	22.82	580
NC80VSL3R3	80.12	2035	57.24	1454	25.82	656
NC86VSL3R3	86.12	2187	63.24	1606	28.82	732
NC92VSL3R3	92.12	2340	69.24	1759	31.82	808
NC53VS	53.12	1349	30.24	768	12.32	313
NC53VF	54.52	1385	30.24	768	12.32	313
NC65VS	65.12	1690	42.24	1073	18.32	465
NC65VF	66.52	1680	42.24	1073	18.32	465
NC92VS	92.12	2340	69.24	1759	31.82	808
NC92VF	93.52	2375	66.24	1682	31.82	808

DUAL DIMENSIONS: INCHES
MILLIMETERS

PANELBOARD COVER
TRIM TYPE 1
SURFACE/FLUSH



DWG# PWFDS-SYTI-0167
NO.