



CERTIFICATE

FOR EUROPEAN PRODUCT SAFETY

Reference No. SE-S-2002559R1

Socket-outlet

Type designation:

230/**

Certificate holder:

Schneider Electric Industries SAS
35 rue Joseph Monier,
92500 Rueil-Malmaison
France

The product complies with the standard(s):

IEC 60884-1:2002+A1+A2
SS 428 08 34:2013+T1
SFS 5610:2015+A11
NEK 502:2016

Date of expiry:

06 November, 2025

Additional information in Appendix

Certification Body:

Intertek Semko AB, Product Certification

Place:

Kista - Stockholm

Signed:

Date:

8 March, 2022

Leif Mattsson

APPENDIX:

Reference No. SE-S-2002559R1

Technical Data:

Type designation	230/***
Rated voltage (V)	250V~
Rated current (A)	16A
IP-Class	IP20, IP21, IP44
Standard sheet	III
Trademark	Schneider Electric
Test Report	2110828STO-001
Product information	Flush type socket-outlet. One-fold, 2P+E, with screwless terminals. With and without shutters. 230/*** (“***” in the type designation can be any character or blank to indicate shipping destination and/or enclosure color, not related to product safety).

Manufacturing Sites: Merten GmbH
Fritz-Kotz Strasse 8, 51674 Wiehl, Germany

Socket-outlet type list:

Antivandalism: (1-gang)

230/S1B7217902

System M-Creativ

230/2300-35

System M (Thermo/Duro)

230/2371, 230/2373, 230/2376, 230/2374, 230/2300, 230/2301, 230/2309 with or without LED light module Mxx2003-0004, 230/2474, 230/2485, 230/2496, 230/2470, 230/2471, 230/2472, 230/2473, 230/2315, 230/2334 with LED light module Mxx2334

System Design (Thermo/Duro)

230/2375, 230/2377, 230/2372, 230/2379 with or without LED light module Mxx2003-0004, 230/2378, 230/2306, 230/2308, 230/2478, 230/2476, 230/2477

APPENDIX:

Reference No. SE-S-2002559R1

System Design (Thermo/Metal)

230/NHA5191702, 230/NHA5200102, 230/NHA2922902, 230/NHA2922002,
230/NHA5191902, 230/NHA5191802, 230/NHA5195702, 230/NHA5191902,
230/NHA5195702/PHA8168102, 230/NHA5195702/NHA5200202,
230/NHA2920902

AQUADESIGN

230/2330, 230/2335

Renova

230/EAV54699

Frame types:

System M (Thermo+Duro)

M-Smart: (1 - 5 gang)
4841, 4842, 4843, 4844, 4845

1M: (1 - 5 gang)

3891, 3892, 3893, 3894, 3895

M-Plan II: (1 - 3 gang)

4881, 5124, 4882, 5125, 4883, 5126

M-Plan: (1 - 5 gang)

4861, 4862, 4863, 4864, 4865

M-Plan Metall: (1 - 5 gang)

4751, 4752, 4753, 4754, 4755

M-Plan real glas: (1 - 5 gang)

4891, 4892, 4893, 4894, 4895

APPENDIX:

Reference No. SE-S-2002559R1

M-Plan real wood: (1-5 gang)

4051, 4052, 4053, 4054, 4055

Atelier-M: (1 - 5 gang)

3881, 3882, 3883, 3884, 3885

System M - Elegance: (1 - 5 gang)

4021, 4022, 4023, 4024, 4025, 4031, 4032, 4033, 4034, 4035

4041, 4042, 4043, 4044, 4045, 4051, 4052, 4053, 4054, 4055

System M - Exxact (Thermo) Basic: (1 - 5 gang)

BBV49550, BBV49551, BBV49552, BBV49553, BBV49554

Design: (1 - 3 gang)

BBV49558, BBV49559, BBV49561

Solid: (1 - 4 gang)

BBV49558, BBV49559, BBV49561, BBV49589

Solid Glass: (1 - 4 gang)

S1A45091, S1A45092, S1A45094, S1A45092

Combi: (1 - 5 gang)

BBV49575, BBV49576, BBV49577, BBV49578, BBV49580

Primo: (1 - 6 gang)

BBV49583, BBV49584, BBV49587, BBV49585, BBV49586, BBV54904, BBV54905

Gasket for all IP44 frames: (1 - 3 gang)

BBV49557, S1A33102, S1A33103

APPENDIX:

Reference No. SE-S-2002559R1

System M – Creative (1 - 5 gang)

4010-35, 4020-35, 4030-35, 4040-35, 4050-35, 4025-35, 4035-35

System Design (Thermo + Duro)

ARTEC, Antik, Fläche: (1 - 5 gang)

4811, 4812, 4813, 4814, 4815, 4831, 3981, 3982, 3983, 3984, 3985

System M – M-Pure (1 - 5 gang)

4010-36, 4020-36, 4030-36, 4040-36, 4050-36

System Design (Thermo + metal + glas/stone)

D-Life (1 - 5 gang)

NHA2920502, NHA2920602, NHA5191402, NHA5191602, NHA2920702

D-Life metal (1 - 5 gang)

NHA2923102, 2xNHA2923302, 2xNHA2923302/1xNHA2923502,
2xNHA2923302/2xNHA2923502, 2xNHA2923302/3xNHA2923502

D-Life glas/basalt (1 - 5 gang)

NHA2922102, NHA2922402, NHA5195402, NHA5195502, NHA2922702

AQUADESIGN: (1 - 4 gang)

4011, 4012, 4013, 4014

Antivandalism (1 - 3 gang)

4801, 4802, 4803

Renova

Glass frame: (1 - 3 gang)

BBV28342, BBV28343, BBV28344

APPENDIX:

Reference No. SE-S-2002559R1

Plastic frame: (1 - 5 gang)

101370, 101371, 101372

Anti Vandalism: (1-gang)

S1B7217902

Robust Screwless (230/***) Socket Outlets, IK class IK09.				Robust: frame
Insert	Center Cover	Center Cover Adapter		
Without Shutters	230/***	101363	101599	101600 (1-gang)
With Shutters		EAV54699		
				

Trend Screwless (230/***) Socket Outlets		
Insert	Center Cover (with Shutters)	Frames
230	NVE66783	100520 (1-gang) 100521 (2-gang) 100522 (3-gang) 100523 (4-gang) 101524 (5-gang)
		

APPENDIX:

Reference No. SE-S-2002559R1

Note: Samples with claw fixings are not applicable for Norway.

This certificate replaces previously issued S-certificate with ref. No. SE-S-2002559 dated 6 November 2020. A new certificate has been issued on account of adding the Norwegian national standard.

Certification Body: Intertek Semko AB, Product Certification **Place:** Kista - Stockholm

Signed:



Leif Mattsson

Date: 8 March, 2022



Intertek