

# Cable Management Rings—AR8121

## Overview


Cable management rings help route cables within an enclosure. The illustrations in this instruction sheet show typical placement of the cable management rings, but placement is not limited to these examples. Use the mounting hardware (provided) to install the cable management rings in your enclosure. Follow the instructions on “How to install and remove caged nuts” on page 3 when installing or removing caged nuts.




Note

Some enclosures will have tapped holes, while others will have square holes. Square holes require the use of caged nuts.


## Inventory



2U cable ring (12)



12-24 × ½-in. screw (24)



M6 × 12 screw (24)



M6 caged nut (24)


## Tools required



Caged nut tool




5-mm hex wrench




Standard screw driver

## 2U cable management ring placement




## Cable management ring placement in NetShelter® VX rear cable channel



## How to identify one U-space on the mounting rail

When installing equipment, locate the top and bottom of a U-space on the mounting rails. Every third hole on the mounting rails of a NetShelter® VX enclosure is numbered to indicate the middle of a U-space. A U-space consists of one of these numbered holes and one hole directly above and below it, as shown.



## How to install and remove caged nuts


*To install a caged nut:*



**Warning**

**Install the caged nut horizontally. Do not install the caged nut vertically with the sides of the caged nut engaging the top and bottom of the square hole.**

1. Insert the caged nut into the square hole by hooking one side of the caged nut assembly through the far side of the hole.
2. Place the caged nut tool (provided) on the other side of the caged nut and pull to snap it into position.



*To remove a caged nut:*

1. Remove any attached screw.
2. Grasp the caged nut and squeeze the sides to release it from the square hole.

## APC Worldwide Customer Support

Customer support for this or any other APC product is available at no charge in any of the following ways:

- Visit the APC Web site to find answers to frequently asked questions (FAQs), to access documents in the APC Knowledge Base, and to submit customer support requests.
  - **www.apc.com** (Corporate Headquarters)
    - Connect to localized APC Web sites for specific countries, each of which provides customer support information.
  - **www.apc.com/support/**
    - Global support with FAQs, knowledge base, and e-support.
- Contact an APC Customer Support center by telephone or e-mail.
  - Regional centers:

Direct InfraStruXure Customer Support Line	(1)(877)537-0607 (toll free)
APC headquarters U.S., Canada	(1)(800)800-4272 (toll free)
Latin America	(1)(401)789-5735 (USA)
Europe, Middle East, Africa	(353)(91)702000 (Ireland)
Japan	(0) 3 5434-2021
Australia, New Zealand, South Pacific area	(61) (2) 9955 9366 (Australia)

- Local, country-specific centers: go to **www.apc.com/support/contact** for contact information.

Contact the APC representative or other distributor from whom you purchased your APC product for information on how to obtain local customer support.

Entire contents copyright © 2003 American Power Conversion. All rights reserved.  
 Reproduction in whole or in part without permission is prohibited. APC, the APC logo, NetShelter, and InfraStruXure are trademarks of American Power Conversion Corporation and may be registered in some jurisdictions. All other trademarks, product names, and corporate names are the property of their respective owners and are used for informational purposes only.

