## APC Back-UPS<sup>®</sup> Pro

Premium Battery Backup with Surge Protection for High Performance Electronics and Computers

900VA, 1200VA, 1500VA



- Reliable
- Energy Efficient
- User Friendly

The Back-UPS Pro series offers your home and business guaranteed power protection for high performance computer systems, routers/modems, external storage devices, game consoles and other electronics.

Abundant backup power, autoshutdown software and protection from damaging surges and spikes are coupled with the Back-UPS Pro's energy saving features, voltage regulation, LCD display and other premium features to make these the perfect units to protect your data and keep you available.



# APC Back-UPS Pro Features 🤇

Standard on all Back-UPS Pro models





LCD (Liquid Crystal Display) gives utility and battery backup the status. Automatic Voltage Regulation (AVR) instantly corrects voltage fluctuations so you can work indefinitely through brownouts and overvoltages. "Battery Backup & Surge Protected" Outlets keep a CPU, monitor and other critical devices running when the power goes out or fluctuates outside safe levels. "Surge Only" Outlets protect printers, faxes or other equipment without reducing battery capacity. (Includes power-saving "Controlled" outlets). Data Line Surge Protection guards against surges and spikes traveling over telephone and network data lines. Auto Shutdown Software allows management of 6 the Back-UPS from your computer Push Button Circuit Breaker enables quick recovery from overloads. 3 Yr Warranty for EU countries - 2 years elsewhere, Equipment Protection Policy where applicable (200,000 AUD, 150,000 Euros, 75,000 GBP), free technical phone and online support. Automatic Diagnostic Testing ensures your unit is 9 ready when you need it. External Battery Pack Compatibility dramatically 10 increases run time. (BR1500G-FR only)



### **APC Back-UPS Pro LCD Display**

Easy to read status of utility and battery backup conditions



**Parameters Displayed:** 

- Input Power (On Battery/On Utility)
- Input Voltage
- Output Voltage
- Output Frequency
- Load (Watts, % of Capacity, Graphic Display)
- Overload
- AVR Working
- System Fault
- Replace Battery
- Battery Charge Status (Graphic Display)
- Estimated Run Time
- Power Saving Mode (Enabled/Disabled)
- Mute (Enabled/Disabled)
- Number of Power Events

### **APC PowerChute® Personal Edition**

Easy-to-use safe system shutdown software with power and energy management features



- Easy to read view of current power conditions.
- Displays daily energy consumption and cost of powering your equipment.
- Saves money by allowing you to choose an energy management plan that fits your needs.
- Prevents data corruption by saving files and shutting down your system during extended power outages or low battery condition.
- Monitors system, and logs utility power problems and battery conditions
- Allows you to configure Back-UPS options like voltage transfer settings, silencing alarms during night hours, shutdown parameters, energy management features, etc.)
- Easy Installation takes the guesswork out of configuration for first-time users with a jargon-free help feature. (USB and serial interface).



#### **Back-UPS Pro Specifications**

Model Number	BR900G-FR	BR1200G-FR	BR1500G-FR
Output			
Output Capacity	900 VA / 540 Watts	1200 VA / 720 Watts	1500 VA / 865 Watts
Output (on utility)	230V, 50 or 60 Hz, +/- 3Hz (auto sensing)		
Output (on battery)	230V +/-8%, 50 or 60 Hz +/-1 Hz (auto sensing)		
Output Connections	6 total French outlets: 3 battery & surge (including 1 power- saving outlet) 3 surge protection only (including 2 power-saving outlets)	6 total French outlets: 3 battery & surge (incl. 1 power- saving outlet) 3 surge protection only (incl. 2 power-saving outlets)	6 total French outlets: 3 battery & surge (incl. 1 power- saving outlet) 3 surge protection only (incl. 2 power-saving outlets)
Waveform Type	Stepped Approximation to Sine Wave		
Input			
Input Voltage, Freq.	230V, 50 or 60 Hz, +/- 3Hz (auto sensing)		
Input Connection	1,8 m power cord with French plug		
Surge Protection			
AC Power	All outlets		
Data Line	Analog phone line for phone/fax/modem/DSL Network: up to 1000 Base-T (gigabit) Ethernet		
Physical			
Unit Dims H x W x D	25,0 x 10,0 x 38,2 cm	30,2 x 11,2 x 38,6 cm	30,2 x 11,2 x 38,6 cm
Unit Weight	11,7 kg	12,8 kg	13.4 kg
Shipping Dims. HxWxD	33,3 x 22,5 x 48,9 cm	38,2 x 23,8 x 48,9 cm	38,2 x 23,8 x 48,9 cm
Shipping Weight	12,8 Kg	13.9 kg	14.5 kg
Color	Black		
UPC Code	731304279594	731304268727	731304268734
Battery			
Battery Type	Sealed, lead-acid, maintenance-free		
External battery pack Compatibility	No	No	Yes (use BR24BPG)
		Management	
Alarms	Visual (LCD) and audible alarms		
Shutdown Software	PowerChute Personal Edition (with USB and serial interface)		
Safety			
Certification/ Approvals	NEMKO-GS, GOST, CE, C-Tick, KETI, TISI, A-Tick	NEMKO-GS, GOST, CE, BS 1363	NEMKO-GS, GOST, CE, BS 1363

APC by Schneider Electric 132 Fairgrounds Rd West Kingston, RI 02892



www.apc.com