

APC Line-R LS Series

Automatic Voltage Regulators

Reliable Protection

Protect your sensitive electronic equipment from brownouts and over voltages with APC Line-R automatic voltage regulators (AVRs).

Uncorrected voltage fluctuations gradually degrade the life of electronic components, potentially causing premature failure.

The Line-R not only adjusts voltages to safe levels, but also provides surge protection against electrical surges, spikes and even lightning.

3 Grounded Outlets Provides reliable AVR protection



Protects users from accidental contact with unused outlets

Extended Input Voltage Range Allows for 230V (184 to 284V)

Power Switch with Built-in Circuit Breaker Easy reset of the circuit breaker

Built-in Surge Protection

148 Joules to protect your devices from damaging surges or spikes.

2-Year Warranty





Technical Specifications

SKU	LS600-FR	LS1000-FR	LS1500-FR
Output			
Output Power Capacity	600VA / 300 W	1000VA / 500W	1500VA / 750W
Nominal Output Voltage	230V		
Voltage Regulation	± 10% @ input range		
Number of Outlets	3		
Outlet Type	French		
Input			
Nominal Input Voltage	230V		
Input Voltage Range	184V to 284V		
Frequency	50Hz ± 5Hz		
Plug Type	French		
Cord Length	1 meter		
Surge Protection			
AVR & Surge Protection	All outlets		
Joule Rating	148 Joules		
Physical			
Unit Dimensions (W x H x D)	180 x 95 x 119 mm		
Unit Weight	1.4 kg	1.6 kg	2.0 kg
Color	Black		
Environment			
Noise level	< 40 dB		
Operating Temperature	32°F to 104°F / 0°C to 40°C		
Humidity	0-90% relative humidity (non-condensing)		
Warranty and Compliance			
Warranty	2 Years		
Certification	CE		



