



Certificate of Compliance

Certificate: 1718289

Master Contract: 157869

Project: 70185839

Date Issued: 2018-05-28

Issued to: Schneider Electric IT Corporation, FKA American Power Conversion Corp.
800 Federal Street
Andover, Massachusetts 01810
USA
Attention: Kin Keat

The products listed below are eligible to bear the CSA Mark shown



Issued by: Sam Zaffino
Sam Zaffino

PRODUCTS

CLASS - C531105 - POWER SUPPLIES-Stand-alone

Uninterruptible Power Supplies;

Model:	Input Rating:	Output Rating:
SMT2200, SUA2200US, SUA2200RMUS, SMT2200RM2U, DLT2200, SMT2200RM2UNC, SMT2KR2UNCX145, SMT2KR2UX145	120V, 60Hz, 19A	120V, 60Hz, 2200VA, 1980W
SMT2200C, SMT2200RM2UC,	120V, 50Hz/60Hz, 19A	120V, 50Hz/60Hz, 2200VA, 1980W
SMT3000, SUA3000US, SMT3000RM2U, DLT3000RM2U, SMT3000RM2UNC, SMT3KR2UNCX145, SMT3KR2UX145	120V, 60Hz, 24A	120V, 60Hz, 2880VA, 2700W
SMT3000C, SMT3000RM2UC,	120V, 50Hz/60Hz, 25A	120V, 50Hz/60Hz, 3000VA, 2700W
SUA3000R2IX38	220-240V, 60Hz, 16A	220-240V, 60Hz, 3000VA, 2700W
Smart-Ups-Ups 450, 450D	120V, 50/60Hz, 7A	120V, 50/60Hz, 280W, 3.75A
Smart-Ups-Ups 700X93, 700RMX176	120V, 50/60Hz, 7A	120V, 50/60Hz, 450W, 5.8A
SU700RMXLNET	120V, 50/60Hz, 12A	120V, 50/60Hz, 450W
SU700X167	120/230V, 60Hz, 10A	120V, 60Hz, 450W, 700VA
SU700R2IX38	220-240V, 60Hz, 7A	220-240V, 60Hz, 450W, 700VA, 3.2A



Certificate: 1718289
Project: 70185839

Master Contract: 157869
Date Issued: 2018-05-28

Model:	Input Rating:	Output Rating:
SU1000RMXLNET, SUA1000US	120V, 50/60Hz, 12A	120V, 50/60Hz, 670W
SU1000X93, SU1000RMX93, SU1000RMX176, SMT1000RM2U SMC10002U	120V, 60Hz, 10A	120V, 60Hz, 670W, 1000VA
SU1400X145, SU1400RMX106, SU1400X106, SU1400RMXLBX120, SU1400RMIX134, SU1400R2UX93, SU1400RMX93, SU1400RMX176, SU1400R2X217, SU1400X93, SU1400R2X180	120V, 50/60Hz, 12A	120V, 50/60Hz, 950W
SU1500RMX155	120V, 60Hz, 15A	120V, 60Hz, 1100W, 1500VA
SU2000RMX155	120V, 60Hz, 20A	120V, 60Hz, 1450W, 2000VA
SU2200XLTX153	208V, 60Hz, 14A	208V, 60Hz, 1600W, 2200VA, 10.57A, 120V, 60Hz, 400W, 400VA, 3.3A
SU2200R3X167	120/230V, 60Hz, 25A	120V, 60Hz, 1600W, 2200VA
SU2200RMI3U	220-230V, 60Hz, 14A	196-253V, 60Hz, 1650W, 2200VA
SU2200RMBX120, SU2200X93, SU3000R3X145, SU3000RMBX120, SU3000X93, SU3000RMBX93	120V, 50/60Hz, 21/24/28A max	120V, 50/60Hz, 2200/2200/3000VA max, 1600/1600/2250W max
SUA1000IX38, SUA1000I	220-240V, 60Hz, 7A	220-240V, 60Hz, 670W, 1000VA, 4.5A
SUA1500IX38, SUA1500I	220-240V, 60Hz, 7A	220-240V, 60Hz, 980W, 1500VA, 6.8A
SUA1500US, SUA1500	120V, 50/60Hz, 12A	120V, 50/60Hz, 980W, 1400VA
SUA2200RMXL3U	110/120Vac, 60Hz, 24A	120Vac, 60Hz, 2200VA, 1980W, 19A
SUA3000RMUS, DLA3000	120V, 60Hz, 24A	120V, 50/60Hz, 2880VA, 2700W
SUA3000RT2X136	100V ac, 60Hz, 30A	100V ac, 60Hz, 2700W, 3000VA, 30A
SUA3000RMXL3U	110/120Vac, 60Hz, 24A	120Vac, 60Hz, 3000VA, 2700W, 24A
SUA5000RMT5U or SUA5KRMT5UX145	208Vac, 60Hz, 24A	208Vac, 60Hz, 5000VA, 4000W, 22A
SURTA1500RMXL2U, SURTA1500RMXL2U-NC	120V, 60Hz, 12A	120V, 60Hz, 1050W, 1500VA, 12A
SURTA2000RMXL2U	120V, 60Hz, 16A	120V, 60Hz, 1400W, 2000VA, 16A
SURTA3000RMXL3U, SURTA3000RMXL3U-NC DLRTA3000RMXL3U	120V, 60Hz, 24A	120V, 60Hz, 2100W, 3000VA, 24A
SURTD3000RMXL3U	200-240V, 60Hz, 16A	200-240V, 60Hz, 2100W, 3200VA, 16A
SURTD5000RMXL3U, SURTD5000RMXLP3U, SURTD5000RMXLJP3U, DLRTD5000RMXL3U	200/208/220/240V, 50-60Hz, 24A	200-240V, 50-60Hz, 3500W, 25A
SURT6000RMXL3U, SURTD6000RMXLP3U, SURTD6000RMXLJP3U, EMC6000R3XLU	200/208/220/240V, 50-60Hz, 20A (30A for hardwired)	200-240V, 50-60Hz, 4200W, 29A
SURT8000RMXL3U	200-240V, 60Hz, 44A	200-240V, 60Hz, 6.4kW, 8kVA, 50A



Certificate: 1718289
Project: 70185839

Master Contract: 157869
Date Issued: 2018-05-28

Model:	Input Rating:	Output Rating:
DLRT8000RMXLT6U		
SURT10000RMXLT6U	200-240V, 60Hz, 50A	200-240V, 60Hz, 8.0kW, 9.6kVA, 48A
SURT192RMXLBP3U	12Vdc, 60Hz, 5Ah	
SURTA48RMXLBP2U	48Vdc, 60Hz, 7.2Ah	
SURT48RMXLBP2U	48Vdc, 60Hz, 7.2Ah	
SMT750RM2U, SMT750RM2UNC	120V, 60Hz, 12A	120V, 60Hz, 750VA, 480W
SMT1500RM2U, SMC15002U, DLT1500RM2U, SMT1500RM2UNC	120V, 60Hz, 12A	120V, 60Hz, 1440VA, 980W
SMT3000RMT2U	208V, 60Hz, 16A	208V, 60Hz, 3000VA, 2700W
SURTA2200RMXL2U-NC	120V,50/60Hz,16A	120V,50/60Hz,1600W,2200VA,16A

APPLICABLE REQUIREMENTS

CSA-C22.2 No. 107.1-01 (Reaffirmed 2011) - General Use Power Supplies -Industrial Products



Supplement to Certificate of Compliance

Certificate: 1718289

Master Contract: 157869 (063938_C_000)

*The products listed, including the latest revision described below,
are eligible to be marked in accordance with the referenced Certificate.*

Product Certification History

Project	Date	Description
70185839	2018-05-28	Update to 1718289 to cover similar models
70129492	2017-03-28	Update to 1718289 to cover addition of similar models
70106496	2016-11-04	Update to CSA report 1718289 to cover alternate model name
70074304	2016-04-22	Update to report 1718289 to cover alternate model names SMT1500 2200 3000RM2UNC
70052526	2016-01-04	Quote for Alternate model SMT750RM2UNC addition for existing CSA certificate :1718289 (LR63938C) and Master Contact 157869
70026860	2015-03-30	Update to add alt names Ocelot CSA SKU addition 1718289
2676543	2013-11-26	Update to cover alternate model names
2652286	2013-08-28	Update to cover addition of alternate model names
2433825	2011-08-31	Update report to cover alternate model names
2195256	2009-07-23	Update project file 2024891 for Canada (CSA Mark)
2024891	2008-04-08	Update Report 1718289 to include new models.
1996999	2008-01-21	Addition of Model (marketing reason only) based on statement of compliance dated Dec.18, 2007.
1979541	2007-12-18	Addition of Model SUA5000RMT5U to report based on existing Model SUA3000RMXL3U done to CSA 107.1-01.
1743931	2006-03-13	Addition of Models from UL Report; Requested Nov. 21/05 E-mail and models SUA2200RMXL3U, SUA3000RMXL3U.
1745282	2006-01-12	Factory Test Correction for UPS
1718289	2005-10-17	Certification Report for Category Models