

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE CERTIFICAT D'ESSAI OC

Product
Produit

Uninterruptible power supply

Name and address of the applicant
Nom et adresse du demandeur

American Power Conversion Corp.
85 Rangeway Road Building #2, NORTH BILLERICA MA 01862
UNITED STATES OF AMERICA

Name and address of the manufacturer
Nom et adresse du fabricant

American Power Conversion Corp.
85 Rangeway Road Building #2, NORTH BILLERICA MA 01862
UNITED STATES OF AMERICA

Name and address of the factory
Nom et adresse de l'usine

APC India Pvt. Ltd.
187/3, 188 Jigani Village Jigani Hobli, 562106 BANGALORE
INDIA

Note: When more than one factory, please report on page 2
Note: Lorsque il y a plus d'une usine, veuillez utiliser la 2^{ème} page

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

☒ Additional Information on page 2

Input: AC 200-240 V; max. 30 A; 50-60 Hz
Output: AC 200-240 V; max. 30 A; 50-60 Hz, max. 4500W
(see Model Matrix)

Trademark (if any)
Marque de fabrique (si elle existe)



Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais constructeur

TMP

Model / Type Ref.
Ref. De type

see Model Matrix

Additional information (if necessary may also be
reported on page 2)
Les informations complémentaires (si nécessaire,
peuvent être indiqués sur la 2^{ème} page)

Class I

☐ Additional Information on page 2

A sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à la

IEC 62040-1(ed.1);corrigendum1

As shown in the Test Report Ref. No. which forms part
of this Certificate
Comme indiqué dans le Rapport d'essais numéro de
référence qui constitue partie de ce Certificat

1924400-3335-0035/191140

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**

VDE Prüf- und Zertifizierungsinstitut GmbH
VDE Testing and Certification Institute
Zertifizierungsstelle / Certification

Date: 2013-11-21

Signature:

E. Biehl

Elcoteq Electronics, (India) Pvt., Ltd.
Block No. VIII, Velankani Information Systems Campus
#43 Electronics City, Phase II, Hosur Road, 560100
BANGALORE
INDIA

APC (India) PVT LTD
No. 18(A), Survey 128, Jigani Village & Hobli Anekal,
Taluk, 562106 BANGALORE
INDIA

East India Packagings Pvt. Ltd. (Electronic Division)
Survey No 17, Kammanahalli Bannerghata Road, 560076
BANGALORE
INDIA

APC (India) PVT LTD
Jigani Village & Hobli Premise 4, No. 73 Survey 103,
ANEKAL, TALUK, 562106 BANGALORE
INDIA

APC (Xiamen) Power Infrastructure Co. Ltd.
1678 JiXian Road, TongAn District, 361100 XIAMEN CITY
CHINA

Additional information (if necessary)
Information complémentaire (si nécessaire)

VDE Prüf- und Zertifizierungsinstitut GmbH
VDE Testing and Certification Institute
Zertifizierungsstelle / Certification

Date: 2013-11-21

Signature:



E. Biehl

CB Certificate: DE1-43132/A4
File Ref.: 1924400-335-0035

MODEL MATRIX

W W W W W X X X X X Y Y Y Y Y Y Y Y Z Z Z Z Z Z

W W W W W = MANUFACTURERS PREFIX A TO Z (may take up to 5 characters)
Low Voltage Isolated Secondary Differences Only(Non-Safety Critical)

X X X X X = VA OUTPUT 0 TO 9 (may take up to 5 characters)
See Current VA Levels below:

2200, 3000, 5000, 6000

Y Y Y Y Y Y Y Y = UNIT CONFIGURATION A TO Z and/or 0 to 9 (may take up to 10 alphanumeric characters)

Current UPS Configurations : I = International, R or RM = Rack Mount, XL = Extended Run, U = Unit Height,
NET = Software in shipping box, PS = Power Switch, B = Black Bezel, BP = Battery Pack, DR = Din Rail Mount

Z Z Z Z Z Z = X followed by up to a three digit number 0 to 9(may take up to 6 characters)[Non safety critical difference only]

Example of how to use Matrix: SURT 3000 XLI
 WWWW XXXXX YYYYYYYY
ZZZZZZ

Product Voltages (all units): 200VAC-240VAC

Product Frequency (all units): 50/60Hz

Maximum Input Current: 30 A

Present Model Prefixes Example: SURT, SMRT, IBM, EMC, SURTD

Example of Models Covered by Matrix:

SURTD2200XLIM, SURT3000XLI-ET, SURTD3000RMXLI, SURTD3000XLI,
SURTD3000XLIM, SURTD5000RMXLI,
SURTD5000XLI, SURTD5000XLI-ET, SURT6000RMXLI,
SURT6000XLI, SURT6000XLI-ET, SURT6000XLIM, DLRTD3000RMXLI3U and
DLRTD5000RMXLI3U