

NetShelter CX

Rack PDU compatibility

Additional power distribution options for your integrated office/home environments:



All NetShelter CX come complete with a basic PDU (**AR4018A/24A/38A, ***AR4018IA/24IA/38IA). APC also provides a wide array of additional power distribution solutions. From additional basic PDUs to options for remote monitoring and/or outlet switching, all your NetShelter CX power distribution needs are covered.

SKU	Input	Output	Type	Mounting	AR4000MV *	AR4018A AR4018IA	AR4024A AR4024IA	AR4038A AR4038IA
AP9551	NEMA L5-20P	(14) 5-20R	Basic	Vertical		X	X	X
AP9559	C20	(10) C13, (2) C19	Basic	Horizontal	X	X	X	X
AP9560	NEMA L5-30P	(10) 5-20R	Basic	Horizontal	X	X	X	X
AP9562	NEMA 5-15P	(10) 5-15R	Basic	Horizontal	X	X	X	X
AP9563	NEMA 5-20P	(10) 5-20R	Basic	Horizontal	X	X	X	X
AP9564	NEMA L5-20P	(10) 5-20R	Basic	Horizontal	X	X	X	X
AP9565	C20	(12) C13	Basic	Horizontal	X	X	X	X
AP9566	NEMA L6-20P	(12) C13	Basic	Horizontal	X	X	X	X
AP9567	NEMA 5-15P	(14) 5-15R	Basic	Vertical		**	**	**
AP9568	C14	(15) C13	Basic	Vertical		***	***	***
AP9570	NEMA L6-30P	(4) C19	Basic	Horizontal	X	X	X	X
AP9571A	NEMA L6-30P	(10) C13	Basic	Horizontal	X	X	X	X
AP9572	C20	(15) C13	Basic	Vertical		X	X	X
AP6002A	NEMA L6-30P	(14) C13, (2) C19	Basic	Vertical			X	X
AP6003A	IEC-320 C20	(14) C13, (1) C20	Basic	Vertical		X	X	X
AP6015A	IEC-320 C14	(8) C13	Basic	Horizontal	X	X	X	X
AP6020A	IEC-320 C20	(13) C14	Basic	Horizontal	X	X	X	X
AP6031A	NEMA L6-30P	(4) C19	Basic	Horizontal	X	X	X	X
AP6032A	IEC 309 32A	(4) C19	Basic	Horizontal	X	X	X	X
AP6037A	NEMA L15-30P	(3) C19	Basic	Horizontal	X	X	X	X
AP6038A	IEC 309 63A	(3) C19	Basic	Horizontal	X	X	X	X
AP6039A	IEC 309 60A	(3) C19	Basic	Horizontal	X	X	X	X
AP6120A	C20	(7) C13, (2) C19	Basic	Horizontal	X	X	X	X
AP6201CH	C20	(8) Chinese outlet	Basic	Horizontal	X	X	X	X
AP6221CH	C20	(12) C13	Basic	Horizontal	X	X	X	X
AP7516	CS8365	(6) C19	Basic	Horizontal	X	X	X	X
AP7526	IEC 309 32A	(6) C19	Basic	Horizontal	X	X	X	X
AP7555A	IEC 309 32A	(3) C13,(6) C19	Basic	Vertical			X	X
AP7567A	CS8365	(3) C13,(6) C19	Basic	Vertical			X	X



•AR4000MV12U (optional EIA mounting rails) is required for horizontal rack PDU mounting

APC®

by Schneider Electric

NetShelter CX

Rack PDU compatibility



SKU	Input	Output	Type	Mounting	AR4000MV *	AR4018A AR4018IA	AR4024A AR4024IA	AR4038A AR4038IA
EPDU1016B	C20	(8) C13	Basic	Horizontal		X	X	X
EPDU1016B-GB	C20	(8) Chinese outlet	Basic	Horizontal		X	X	X
EPDU1116B	IEC 309 16A	(20) C13, (4) C19	Basic	Vertical			X	X
EPDU1116B-SCH	Schuko CEE 7	(14) Schuko CEE 7	Basic	Vertical			X	X
EPDU1132B	IEC 309 32A	(20) C13, (4) C19	Basic	Vertical				X
EPDU1132B-SCH	IEC 309 32A	(21) Schuko CEE 7	Basic	Vertical				X
AP7800B	NEMA 5-15P	(8) 5-15R	Metered	Horizontal	X	X	X	X
AP7801B	NEMA L5-20P	(8) 5-20R	Metered	Horizontal	X	X	X	X
AP7802B	NEMA L5-30P	(16) 5-20R	Metered	Horizontal	X	X	X	X
AP7811B	NEMA L6-30P	(12) C13, (4) C19	Metered	Horizontal	X	X	X	X
AP7820B	C14	(8) C13	Metered	Horizontal	X	X	X	X
AP7821B	C20	(8) C13	Metered	Horizontal	X	X	X	X
AP7822B	IEC309-32A	(12) C13, (4) C19	Metered	Horizontal	X	X	X	X
AP8831	NEMA 5-15P	(16) 5-15R	Metered	Vertical				X
AP7850B	C14	(16) C13	Metered	Vertical				X
AP8858	C20	(18) C13, (2) C19	Metered	Vertical			X	X
AP7802BJ	NEMA L5-30P	(16) 5-15R	Metered	Horizontal	X	X	X	X
AP8833J	NEMA L5-20P	(10) 5-15R	Metered	Vertical			X	X
AP8858NA3	NEMA L6-20P	(18) C13,(2) C19	Metered	Vertical			X	X
AP8858EU3	IEC 309 16A	(18) C13,(2) C19	Metered	Vertical			X	X
EPDU1016M	C20	(8) C13	Metered	Horizontal		X	X	X
EPDU1116M	IEC 309 16A	(18) C13, (3) C19	Metered	Vertical			X	X
EPDU1132M	IEC 309 32A	(20) C13, (4) C19	Metered	Vertical				X
AP7900B	NEMA 5-15P	(8) 5-15R	Switched	Horizontal	X	X	X	X
AP7901B	NEMA L5-20P	(8) 5-20R	Switched	Horizontal	X	X	X	X
AP7902B	NEMA L5-30P	(16) 5-20R	Switched	Horizontal	X	X	X	X
AP7911B	NEMA L6-30P	(16) C13	Switched	Horizontal	X	X	X	X
AP7920B	C14	(8) C13	Switched	Horizontal	X	X	X	X
AP7921B	C20	(8) C13	Switched	Horizontal	X	X	X	X
AP7922B	IEC309-32A	(16) C13	Switched	Horizontal	X	X	X	X
AP8931	NEMA 5-15P	(16) 5-15R	Switched	Vertical				X
AP7950B	C14	(16) C13	Switched	Vertical				X
AP8958	C20	(7) C13, (1) C19	Switched	Vertical				X
AP7902BJ	NEMA L5-30P	(16) 5-15R	Switched	Horizontal	X	X	X	X
AP8958NA3	NEMA L6-20P	(7) C13,(1) C19	Switched	Vertical				X
AP8958EU3	IEC 309 16A	(7) C13,(1) C19	Switched	Vertical				X



•AR4000MV12U (optional EIA mounting rails) is required for horizontal rack PDU mounting



by Schneider Electric

NetShelter CX

Rack PDU compatibility



SKU	Input	Output	Type	Mounting	AR4000MV *	AR4018A AR4018IA	AR4024A AR4024IA	AR4038A AR4038IA
SPD10K	Hard Wire 3 wire	(8) C13,(2) C19, (4) Hard wire	Smart	Horizontal	X	X	X	X
SPD10KCB	Hard Wire 3 wire	(8) C13,(2) C19, (4) Hard wire	Smart	Horizontal	X	X	X	X
SPD10KCBL	Hard Wire 3 wire	(8) C13,(2) C19, (4) Hard wire	Smart	Horizontal	X	X	X	X
SPD20K	Hard Wire 3 wire	(6) C13,(1) C19, (6) Hard wire	Smart	Horizontal	X	X	X	X
SPD20KCB	Hard Wire 3 wire	(6) C13,(1) C19, (6) Hard wire	Smart	Horizontal	X	X	X	X
SPD20KCBL	Hard Wire 3 wire	(6) C13,(1) C19, (6) Hard wire	Smart	Horizontal	X	X	X	X
SPD5K	Hard Wire 3 wire	(8) C13,(2) C19, (4) Hard wire	Smart	Horizontal	X	X	X	X
SPD5KCB	Hard Wire 3 wire	(8) C13,(2) C19, (4) Hard wire	Smart	Horizontal	X	X	X	X
SPD5KCBL	Hard Wire 3 wire	(8) C13,(2) C19, (4) Hard wire	Smart	Horizontal	X	X	X	X
AP4421	C14	(12) C13	Auto Transfer Switch	Horizontal	X	X	X	X
AP4422	IEC 309 16A	(1) IEC 309 16A	Auto Transfer Switch	Horizontal	X	X	X	X
AP4423	C20	(8) C13,(1) C19	Auto Transfer Switch	Horizontal	X	X	X	X
AP4424	IEC 309 32A	(16) C13,(2) C19	Auto Transfer Switch	Horizontal	X	X	X	X
AP4430	NEMA L6-20P	(8) C13,(1) C19	Auto Transfer Switch	Horizontal	X	X	X	X
AP4431	NEMA L6-30P	NEMA L6-30R	Auto Transfer Switch	Horizontal	X	X	X	X
AP4432	NEMA L6-30P	(16) C13,(2) C19	Auto Transfer Switch	Horizontal	X	X	X	X
AP4433	C14	(12) C13	Auto Transfer Switch	Horizontal	X	X	X	X
AP4434	C20	(8) C13,(1) C19	Auto Transfer Switch	Horizontal	X	X	X	X
AP4450	NEMA 5-15P	(10) NEMA 5-15R	Auto Transfer Switch	Horizontal	X	X	X	X
AP4452	NEMA L5-20P	(10) NEMA 5-20R	Auto Transfer Switch	Horizontal	X	X	X	X
AP4452J	NEMA L5-20P	(8) NEMA 5-15R	Auto Transfer Switch	Horizontal	X	X	X	X
AP4453	NEMA L5-30P	(16) NEMA 5-20R	Auto Transfer Switch	Horizontal	X	X	X	X
AP7750A	NEMA 5-15P	(10) NEMA 5-15R	Auto Transfer Switch	Horizontal	X	X	X	X



•AR4000MV12U (optional EIA mounting rails) is required for horizontal rack PDU mounting

APC®

by Schneider Electric