



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**T02CN23G7**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

Max. Continuous Current Rating: 600V / 27A  
 Certifications: UL Listed, CSA, CE  
 RoHS: Yes  
 Termination Method: Screw Clamp  
 Weight (lbs): 2.09  
 Power Wire Size (AWG): #6 - #14  
 Control Wire Size (AWG): #10 - #18  
 Mounting: 35mm DIN Rail, Panel

**Specification:**

Description: TeSys N Rev. Contactor Sz1 3P 120VAC  
 Type: FVR  
 Voltages Code: G7 at 120VAC

Coil Consumption: Inrush 70 VA  
 Sealed 7 VA

Single Phase		Three Phase			
115V	230V	200V	230V	460V	575V
2 HP	3 HP	7.5 HP	7.5 HP	10 HP	10 HP