



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
TM2ALM3LT

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:
 Resolution: 12 bits or 11 bits + sign (4096 points) (INPUT), 12 bits (4096 points) (OUTPUT)
 Input Acquisition Period: 50ms + 1 Controller Cycle Time
 Output Transfer Time: 20ms + 1 Controller Cycle Time
 Isolation Between Channels and Int. Logic: 500V AC rms
 Isolation Between Channels: Non Isolated Between Channels, 500V AC rms (Channel and Sensor Supply)
 Mounting: 35mm DIN Rail
 RoHS: Yes
 Weight [kg]: 0.085

Description:
 Selection: Analog Mixed Expansion Module
 Input Range: Thermocouple type J, K and T, Temp probe 2 or 3 Wire Pt100 = -100C-500C)
 Output Range: 0-10V, 4-20mA
 Connection Type: Removable Screw Terminal Block

Specification: