



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**TM2DDO8TT**

Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**  
 Isolation Between Channels and Int. Logic: 500V AC rms for 1min  
 Isolation Between Channels: N/A  
 Mounting: 35mm DIN Rail  
 RoHS: Yes  
 Weight [kg]: 0.085

**Description:**  
 Selection: Digital Output Expansion Module  
 Input Voltage Range: N/A  
 Input Current: N/A  
 Input Logic: 20.4 - 28.8V DC  
 Output Logic: Sinking  
 Output Current (per output/per group of channels): 0.5A max/4A at 28.8V  
 Output Logic: Source  
 Num. of Relay Outputs: 0  
 Response Time (Off-On/On-Off): 0.45ms/0.45ms  
 Connection Type: Removable Screw Terminal Block

**Specification:**