

# UK DECLARATION OF CONFORMITY




by Schneider Electric

We: **Manufacturer**  
**Schneider Electric Japan Holdings Ltd.**  
**Subsidiary of Schneider Electric Industries SAS (FR -92500 Rueil-Malmaison)**  
**4-4-9 Kitahama, Chuo-ku, Osaka, 541-0041 Japan**

**UK Representative**  
**Schneider Electric Limited**  
**Stafford Park 5**  
**Telford, TF3 SBL - United Kingdom**

Hereby declare under our sole responsibility that the products:

<b>Trademark</b>	Pro-face 
<b>Product, Type, Function</b>	HMI Industrial Controller
<b>Models</b>	PFXPSA6000 series, PFXPSA6A7D, PFXPSA6AED, PFXPSA6AFD PFXPSA65FD, PFXPSA65GD  Includes models with additional alphanumeric characters at the end of the model number. See detailed list of references

are in conformity with the requirements of the following directives and conformity was checked in accordance with the following standards:

Regulation	Designated standard / Notified body reference
The Electromagnetic Compatibility Regulation <b>SI 2016 No. 1091</b>	<b>EN 61131-2:2007</b> Programmable controllers - Part 2: Equipment requirements and tests Other standard considered: IEC 61131-2:2017
The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 <b>SI 2012 No. 3032</b>	<b>EN IEC 63000:2018</b> Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances.

Subject to correct installation, maintenance and use conforming to its intended purpose, to the applicable regulations and standards, to the supplier's instructions, user manual and to accepted rules of the art.

Issued at:  
 Telford – United Kingdom April 6th, 2026

Name(\*):

Signed by:  
  
A578D60923D7459...  
 David WILLIAMS  
 VP Marketing UK&I – Zone UK & Ireland

(\* ) Name and title of the signatory empowered to bind the manufacturer or his authorized representative.

# UK DECLARATION OF CONFORMITY

by **Schneider Electric**

## List of references

Digit	1-7	8	9	10	11	12	13-15	16 and after
Range	PFXPSA6							
CPU	Atom	A						
	Core i5	5						
Display	15"		7					
	12" Wide		E					
	15" Wide		F					
	19" Wide		G					
Power	24Vdc			D				
Storage	128GB				1			
	Reserved "*" Any letter or number				*			
Memory	8GB					8		
	Reserved "*" Any letter or number					*		
OS	Windows 11 IoT						W11	
	Reserved "*" Any letter(s) or number(s)						*	
Reserved	Reserved "*" Any letter(s), number(s) or blank							*

## List of options and accessories

Product Number	Product Name
<b>Storage</b>	
PFXYPSA6M2128L	M.2 SSD 128 GB (Type 2280)
PFXYPSA6M2512L	M.2 SSD 512 GB (Type 2280)
HMIYPSA6NVM256	M.2 SSD 256 GB (Type 2280)
<b>Cable</b>	
PFXYFPCBDPDV5M	DP-DVI Cable 5 m
PFXYP6CVUSAU	USB/Audio Conversion Cable

End